


**Part Number: 91525-8454**

0.50mm Pitch LaneLink™ I/O Latch Receptacle, 4 Lane, Cx4 Ethernet, 8 Circuits, 4 Solder Posts, Panel Mount, Tape and Reel Packaging



Series image - Reference only

<b>Status:</b>	<b>OBsolete</b>
<b>Replacement:</b>	918048454 Foam Gasket, <a href="#">918048455</a> Metal Gasket
<b>Series:</b>	<a href="#">91525</a>
<b>Category:</b>	I/O Connectors

**Mates With Part(s):**  
[916351020](#), [916351021](#), [916351022](#)**Product Environmental Compliance****EU RoHS:** ELV and RoHS Compliant**China RoHS:** **REACH SVHC:****Low-Halogen Status:** Not Reviewed**Part Detail****General**

<b>Status</b>	<b>Obsolete</b>
Category	I/O Connectors
Series	<a href="#">91525</a>
Application	Wire-to-Board
Component Type	Receptacle
Product Name	InfiniBand*, LaneLink™
Type	N/A

**Physical**

Circuits (Loaded)	8
Circuits (maximum)	8
Circuits Detail	8 Differential Pair
Color - Resin	Black
Durability (mating cycles max)	250
Lock to Mating Part	Yes
Material - Metal	Brass, Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm, 2.40mm, 4.00mm
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
Pitch - Mating Interface	0.50mm
Plating min - Mating	0.102µm
Plating min - Termination	3.048µm
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-20°C to +60°C
Termination Interface: Style	Surface Mount
Wire Size AWG	N/A

**Electrical****(Please review the Product Specification for specific details.)**

Current - Maximum per Contact	0.5A
Grounding to Panel	Screw Hole
Shielded	Yes
Voltage - Maximum	30V

**Solder Process Data**

Lead-free Process Capability	Reflow Capable (SMT only)
Process Temperature max. C	260

**Material Info**

UPC	822348246724
-----	--------------

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

---

**Previously Available Application****Tooling**

[Check our list of old tooling that used to be available for this part](#)