



Series 804 Push-Pull Mighty Mouse Receptacle Connector

804-003 and 804-004 Ordering Information



In-Line

Rear Panel Mount
Jam NutFront Panel Mount
Jam Nut

Integral Band Platform

for direct attachment of a cable shield. Install a boot, or overmold directly onto the band platform. Or, choose an accessory thread for attaching strain reliefs and backshells.

Three Shell Styles

Jam nut with O-ring for front or rear panel mounting, or in-line receptacles for free-hanging cables.

Watertight, Shielded

O-ring inside the receptacle provides a dynamic seal when mated. Gold-plated spring provides secure mechanical retention and low shell-to-shell resistance for excellent EMI shielding.

How To Order

Sample Part Number		804-003	-01	M	7-10	P
Series (See Table I)	804-003 = Receptacle with Banding Platform 804-004 = Receptacle with Accessory Thread					
Shell Style (See Table II)	-00 = Front Panel Mount Jam Nut (See Table V) -01 = In-Line -07 = Rear Panel Mount Jam Nut (See Table IV)					
Shell Material and Finish	C = Aluminum / Black Anodize (Non-Conductive); RoHS Compliant M = Aluminum / Electroless Nickel; RoHS Compliant MT = Aluminum / Nickel-PTFE RoHS Compliant NF = Aluminum / Cadmium with Olive Drab Chromate ZNU = Aluminum / Zinc-Nickel with Black Chromate Z1 = Stainless Steel / Passivated; RoHS Compliant					
Shell Size - Insert Arrangement	See Contact Arrangements Page G-2					
Contact Type	Connector supplied without contacts A = Pin, Crimp B = Socket, Crimp Connectors with contacts are supplied with signal and/or power crimp contacts. These contacts are not installed. Coaxial contacts and non-standard signal contacts are ordered separately.		Connector supplied Crimp contacts P = Pin Connector S = Socket Connector	Connector Supplied with 30 AWG Crimp Barrel G = Pin, Crimp H = Socket, Crimp		
Shell Key Positions (See Table III)	Omit = Single Master Key A = Normal B = Pos. B C = Pos. C D = Pos. D E = Pos. E F = Pos. F					

Table I: Series

804-003 Receptacle with Banding Platform	804-004 Receptacle with Accessory Thread

Table II: Shell Style

-00 Jam Nut for Front Panel Mounting	-01 In-Line for Free-Hanging Cable	-07 Jam Nut for Rear Panel Mounting


Dimensions in Inches (millimeters) are subject to change without notice.

Series 804 Push-Pull Mighty Mouse Receptacle Connector 804-004-07 and 804-003-07 Dimensions



Series 804

Jam nut, rear panel mount receptacle - shell style 07



1. Grommet protrudes for power/combo arrangements

Integral Band Platform
804-003-07

Accessory Thread
804-004-07

Dimensions												
Shell Size	A Thread	Ø B		Ø C		D Flat		Ø E		Ø F		T Threads
		In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	
5	.4375-32 UN-2A	.790	20.07	.562	14.27	.415	10.54	.246	6.25	.450	11.43	.2500-32 UNEF-2A
6	.5000-32 UN-2A	.830	21.08	.625	15.87	.467	14.40	.286	7.26	.480	12.19	.3125-32 UNEF-2A
7	.6250-28 UN-2A	.900	22.86	.750	19.05	.594	15.09	.390	9.91	.580	14.73	.4375-28 UNEF-2A
8	.6250-28 UN-2A	.900	22.86	.750	19.05	.594	15.09	.442	11.23	.603	15.32	.5000-28 UNEF-2A
9	.6875-28 UN-2A	1.000	25.40	.812	20.62	.655	16.64	.500	12.70	.695	17.65	.5625-24 UNEF-2A
10	.7500-28 UN-2A	1.085	27.48	.875	22.22	.721	18.31	.564	14.33	.735	18.67	.6250-24 UNEF-2A
11	.8125-28 UN-2A	1.135	28.83	.938	23.83	.788	20.02	.608	15.44	.810	20.57	.6875-24 UNEF-2A
12	.8750-28 UN-2A	1.180	29.97	1.000	25.40	.843	21.41	.650	16.51	.880	22.35	.6875-24 UNEF-2A
14	1.0000-28 UN-2A	1.325	33.66	1.125	28.57	.968	24.59	.805	20.45	1.010	25.65	.9375-20 UNEF-2A

Table III: Alternate Key Positions

Pos.	A°	B°
A	150°	210°
B	75°	210°
C	95°	230°
D	140°	275°
E	75°	275°
F	95°	210°

Rear Mount Jam Nut Panel Cutout

Shell Size	A Flat		Ø B	
	In. ± .002	mm. ± 0.05	In. ± .005	mm. ± 0.13
5	.427/.423	10.85/10.74	.448	11.38
6	.479/.475	12.17/12.07	.510	12.95
7	.606/.602	15.39/15.29	.635	16.13
8	.606/.602	15.39/15.29	.635	16.13
9	.667/.663	16.94/16.84	.695	17.65
10	.734/.729	18.64/18.52	.760	19.30
11	.801/.796	20.35/20.22	.822	20.88
12	.855/.851	21.72/21.62	.885	22.48
14	.980/.976	24.89/24.79	1.010	25.65


Dimensions in Inches (millimeters) are subject to change without notice.



Series 804 Push-Pull Mighty Mouse Receptacle Connector

804-004-00 and 804-003-00 Dimensions

Jam nut, front panel mount receptacle - shell style 00



1. Grommet protrudes for power/combo arrangements

Integral Band Platform
804-003-00

Accessory Thread
804-004-00

Shell Size	Ø A		B Threads		C Threads		Ø D		Ø E		F Flat	
	In.	mm.					In.	mm.	In.	mm.	In.	mm.
5	.830	21.08	.5000-32 UN-2A	.2500-32 UNEF-2A	.246	6.25	.625	15.87	.470	11.94		
6	.885	22.48	.5625-32 UN-2A	.3125-32 UNEF-2A	.286	7.26	.688	17.47	.530	13.46		
7	.995	25.27	.6875-28 UN-2A	.4375-28 UNEF-2A	.390	9.91	.812	20.62	.663	16.84		
8	.995	25.27	.6875-28 UN-2A	.5000-28 UNEF-2A	.442	11.23	.812	20.62	.663	16.84		
9	1.075	27.31	.7500-28 UN-2A	.5625-24 UNEF-2A	.500	12.70	.875	22.22	.720	18.29		
10	1.140	28.95	.8125-28 UN-2A	.6250-24 UNEF-2A	.564	14.33	.938	23.82	.788	20.02		
11	1.190	30.23	.8750-28 UN-2A	.6875-24 UNEF-2A	.608	15.44	1.000	25.4	.843	21.41		
12	1.340	34.04	1.0000-28 UN-2A	.6875-24 UNEF-2A	.650	16.51	1.125	28.57	.970	24.64		
14	1.390	35.31	1.0620-20 UN-2A	.9375-20 UNEF-2A	.805	20.45	1.162	29.51	1.020	25.91		

Front Mount Jam Nut Panel Cutout				
Shell Size	A Flat		Ø B	
	In. ± .002	mm. ± 0.05	In. ± .005	mm. ± 0.13
5	.482 .478	12.24 12.14	.510	12.95
6	.542 .538	13.77 13.67	.575	14.61
7	.676 .671	17.17 17.04	.698	17.73
8	.676 .671	17.17 17.04	.698	17.73
9	.732 .728	18.59 18.49	.760	19.30
10	.801 .796	20.35 20.22	.822	20.88
11	.855 .851	21.72 21.62	.885	22.48
12	.982 .978	24.94 24.84	1.010	25.65
14	1.032 1.028	26.21 26.11	1.075	27.31


Dimensions in Inches (millimeters) are subject to change without notice.

Series 804 Push-Pull Mighty Mouse Receptacle Connector 804-004-01 and 804-003-01 Dimensions



Series 804

Cable receptacle - shell style 01



1. Grommet protrudes for power/combo arrangements

Integral Band Platform 804-003-01

Accessory Thread 804-004-01

Dimensions					
Shell Size	Ø A		Ø B		C Threads
	In.	mm.	In.	mm.	
5	.246	6.25	.450	11.43	.2500-32 UNEF-2A
6	.286	7.26	.480	12.19	.3125-32 UNEF-2A
7	.390	9.91	.580	14.73	.4375-28 UNEF-2A
8	.442	11.23	.603	15.32	.5000-28 UNEF-2A
9	.500	12.70	.695	17.65	.5625-24 UNEF-2A
10	.564	14.33	.735	18.67	.6250-24 UNEF-2A
11	.608	15.44	.810	20.57	.6875-24 UNEF-2A
12	.650	16.51	.880	22.35	.6875-24 UNEF-2A
14	.805	20.45	1.010	25.65	.9375-20 UNEF-2A

Dimensions in Inches (millimeters) are subject to change without notice.