






NOTES:


1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 3A @120V or 28VDC;
1A @250VAC
5. FIXED TERM. & MOVING CONTACT:
Copper Alloy w/SILVER plate.
6. PLUNGER AND BODY: UL94 V0
7. CONTACT RESISTANCE:
20mILLI-ohms initial @2-4VDC.
8. ELECTRICAL LIFE: 60,000 make-and-break
cycles at full load.
9. INSULATION RESISTANCE: 1,000M ohm min.
10. DIELECTRIC STRENGTH: 1000V RMS @sea level
11. OPERATING TEMP.: -30°C to 85°C



CIRCUIT: SPDT

SWITCH FUNCTION	
DN	(DN)
2-1	2-3

() = MOMENTARY



RECOMMENDED P.C.B. LAYOUT

			TITLE			
			800 SP-8 B10 M7 Q E/C1 RED (UL94V0)			
A	13270	RELEASED FOR PRODUCTION	7/7/03	AR		
REV.	ECN NO.	DESCRIPTION	DATE	CHKD		
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED						
SCALE			DATE	DR	DWG	REV
2:1			7/7/03	AR	XT0096P	A