




Subminiature Fuses
Type 172593
quick-acting F



Standards
UL 248-14

Approvals
UL US



Pre-arcing time/current characteristic (at Ta 23 °C)

Table with 4 columns: n · In, 1 · In, 2 · In, 3 · In. Row 1: Rated current In. Row 2: Time (t > 4 h, t ≤ 60 s, t ≤ 0,1 s).

Table with 6 columns: Order No., Rated current In / Rated voltage Un, Breaking capacity, Voltage drop at In, Pre-arcing I²t at max. 10 · In, Approvals. Rows include various fuse types and ratings (e.g., 50 A / 250 V AC, 300 A / 125 V AC).

XX Index for packaging
Packaging see page 81