

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

50753-8041

Status:


Active

Overview:

PanelMate™ Wire-to-Board Connector System

Description:

PanelMate™ Crimp Terminal 50753, 30-32 AWG, Reel



Documents:

Drawing (PDF)	Product Specification PS-51146-009 (PDF)
Product Specification PS-51146-001 (PDF)	Product Specification PS-51146-010 (PDF)
Product Specification PS-51146-006 (PDF)	Product Specification PS-51146-011 (PDF)
Product Specification PS-51146-007 (PDF)	Product Specification PS-51146-012 (PDF)
Product Specification PS-51146-008 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	50753
Application	Signal
Crimp Quality Equipment	Yes
Overview	PanelMate™ Wire-to-Board Connector System
Product Name	PanelMate™
UPC	800753369887
Physical	
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	14.300/mg
Packaging Type	Reel
Plating min - Mating	0.203µm
Plating min - Termination	0.203µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.40-0.55mm
Wire Size AWG	30, 32
Wire Size mm²	N/A

Material Info	
Reference - Drawing Numbers	
Product Specification	PS-51146-001, PS-51146-006, PS-51146-007, PS-51146-008, PS-51146-009, PS-51146-010, PS-51146-011, PS-51146-012, RPS-51146-004, RPS-51146-007, RPS-51146-008, RPS-51146-013, RPS-51146-015, RPS-51146-017, RPS-51146-018, RPS-51146-019, RPS-51146-020, RPS-51146-021, RPS-51146-022, RPS-51146-023, RPS-51146-024, RPS-51146-025, RPS-51146-026, RPS-51146-027, RPS-51146-029, RPS-51146-031, RPS-51146-035 SD-50753-8****
Sales Drawing	

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series	
50753Series	
Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Hand Crimp Tool, UL	0638117900
Approved	
Fine Adjust	0639027900
Applicator	
PanelMate™ Crimp	
Terminals	
Extractor Tool for	0638133400
1.25mm Pitch Wire-	
to-Board Crimp	
Terminal	
Japan	
Description	Product #

Applicator for M211A 0573523000
Bench Press, 28-30
AWG Wire
Side-Feed Applicator 0573523200
For Full-Auto
Machine

This document was generated on 09/11/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[50753-8041](#)