



NOTES:

MATERIAL



1. Insulator Material: Glass-filled thermoplastic PBT, UL94V-0
2. Contact Material: Copper alloy
3. Shell : SPCC

ELECTRICAL

- 1.Current Rating : 1AMP
- 2.Voltage Rating : 250V AC/rms 60Hz
- 3.Contact Resistance: 20mΩ Max at 1 AMP DC
- 4.Insulation Resistance: 1000MΩ min at 500 VDC
- 5.Withstand Voltage: 1000V AC/rms 60Hz for 1 minute



50 Positions



Dimensions

Positions	A±0.15	B±0.10	C±0.15	E±0.08	F±0.10
09	30.81	24.99	16.92	11.08	19.20
15	39.14	33.32	25.50	19.39	27.70
25	53.04	47.04	38.96	33.24	41.10
37	69.32	63.50	55.42	49.86	57.30

RoHS compliant

Unit: mm



File No.: E198287

Scale	1:1					Date	Name	Customer-No.		G
TOLERANCE						Drawn	26.12.2008	Dean	ASSMANN WSW-No. A-DS XX PP-F	
X.	±0.38					Approved	26.12.2008	Hellwig		
X.X	±0.25									
X.XX	±0.13								Drawing-No. ASS 3263 CO	rev01
DIM	TOL									
X.°	±3°									
X.X°	±1.0°	①	Drawn	26.12.2008	Dean				Replace	Sheet
Angle	TOL	Id.	Modification	Date	Name					