





CATALOG LISTING
602HE126-6B
PAGE 1 OF 1
REPLACES
PR-23263
CHECK
JJA
12 MAR 98
CHECK
JAK
4 MAR 98
DRAWN
DDM/CAD

ISSUE
3
CHECK
JJA
12 MAR 98
CHECK
JAK
4 MAR 98

REVISIONS
A PR23263
JAK
4 MAR 98
B C093159
D L T
8 JUN 98



CIRCUIT DIAGRAM

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH			THIRD ANGLE PROJECTION 	
CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL
OPERATING FORCE — — — — 5 —12 LB		CONTACT ARRANGEMENT 2X S P D T GOLD CONTACTS		DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE --- 30 LB MAX				
RELEASE FORCE — — — — — 3 LB MIN		LOAD	28 VDC	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
PRETRAVEL — — — — — .040 MAX			SEA LEVEL & 50,000 FT.	
DIFFERENTIAL TRAVEL — — — .020 MAX		RES	1.0	
OVERTRAVEL — — — — — — .100 MIN		IND	0.5	
		MOTOR		
				WEIGHT

- NOTES
- 1 – CORROSION RESISTANT STEEL ENCLOSURE
 - 2 – SWITCH SEALED PER MIL-S-8805 SYMBOL 5
 - 3 – COINCIDENCE OF OPERATING AND RELEASING POINTS: $.010$ INCH OF PLUNGER TRAVEL
 - 4 – CIRCUIT DIAGRAM, AND CATALOG LISTING SHOWN ON NAMEPLATE
 - 5 – REPLACEMENT MOUNTING HARDWARE – PACKET 19PA9
 - 6 – FOR OPERATION IN TEMPERATURE OF MINUS 65°F TO PLUS 257°F
 - 7 – HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805
 - 8 – ENCLOSURE FINISHED WITH WHITE EPOXY BASED ENAMEL COLOR COLOR NO. 37875 PER FEDERAL STANDARD 595

ANSI Y14.5M-1982 APPLIES

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[602HE126-6B](#)