







- NOTES**
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - CIRCUIT DIAGRAM, DATE CODE, FED MFG CODE AND CAT. LIST. ARE SHOWN ON NAMEPLATE
 - 3 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
 - 4 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
 - 5 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 2

NO PLACES	ONE PLACE	TWO PLACES	THREE PLACES	ANGLES
1.04	0.41/0.18	0.16/0.008	0.07/0.003	0.002/0.001

DESIGN UNITS ☐ SI METRIC ☒ US CUSTOMARY

RAW MATERIAL - COMMERCIAL STANDARD
MICRO SWITCH STANDARDS APPLY
DIMENSIONS ARE TO BE MET BEFORE
PROTECTIVE COATINGS ARE APPLIED

WEIGHT 7.9 OZ MAX

CHARACTERISTICS

OPERATING FORCE ----- 6-12 LB
FULL OVERTRAVEL FORCE ----- 30 LB MAX
RELEASE FORCE ----- 4 LB MIN
PRETRAVEL ----- .040 MAX
DIFFERENTIAL TRAVEL ----- .020 MAX
OVERTRAVEL ----- .125 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
SPDT (2)

LOAD	SEA LEVEL	50,000 FT.
RES	7	7
IND	4	2.5
MOTOR	4	

602EN14-6
PAGE 1 OF 1
RELEASE NO. SR-11449
DRAWING NUMBER
18
ISSUE
REVISIONS
A C046610
D J W
9 OCT 79
B C047573
J A P
7 AUG 80
C C049806 C
K A G
28 SEP 81
D C0-55924
C E C
20 SEPT 84
E C057370
J A P
14 MAY 85
F C0-75612-8
W E S
16 AUG 93
G C0-93765
P P F
30 NOV 98
FO-32851-A
DRAWN
D J W
9 OCT 79
CHECK
D J W
9 OCT 79
CHECK
D J W
9 OCT 79
CHECK

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[602EN14-6](#)