






- ① HOUSING: LCP, UL94V-0, BLACK.
CONTACT: PHOSPHOR BRONZE.
POST: BRASS WIRE.
- ② CONTACT: 0.76 μ m GOLD PER ASTM B 488 IN
CONTACT AREA.
1.27 μ m MIN TIN-LEAD
ON PCB TAIL,
OVER 1.27 μ m MIN NICKEL PER
SAE AMS-QQ-N-290 OVER ALL.
POST: 1.27 μ m MIN NICKEL.
- ④ CONTACT: 0.76 μ m GOLD PER ASTM B 488 IN
CONTACT AREA,
0.50 μ m MIN MATTE TIN PER ASTM B 545
ON PCB TAIL,
OVER 1.27 μ m MIN NICKEL PER
SAE AMS-QQ-N-290 OVER ALL.
POST: 1.27 μ m MIN NICKEL.
- ⑥ POWER PIN PAIRS INDICATED ARE COMMONED
INSIDE ASSEMBLY.



4	9 SINGLE END, NONSEQUENTIAL WAFERS AND 7 POWER WAFER	1410997-2
2	9 SINGLE END, NONSEQUENTIAL WAFERS AND 7 POWER WAFER	1410997-1
FINISH	DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN D. CARRO		25JUL2006		 TE Connectivity	
		C. GRIFFITH		25JUL2006			
DIMENSIONS:		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME		RIGHT ANGLE PLUG ASSEMBLY, LEFT END, FULL, 25.4mm, POWER COMBINATION MULTIGRIT RTI, DAUGHTERCARD CONNECTOR	
mm		mm		PRODUCT SPEC			
		0 PLC $\pm$		108-2072		SIZE CAGE CODE DRAWING NO A100779C=1410997	
		2 PLC ± 0		APPLICATION SPEC			
		2 PLC ± 0.13		114-13056		RESTRICTED TO	
		2 PLC ± 0.013		WEIGHT			
MATERIAL		FINISH		CUSTOMER DRAWING		SCALE 8:1 SHEET 1 OF 1 REV C	
							