




All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to
Mechanically compatible with

IEC 60169-23
RPC-2.92 and SMA

Documents

N/A

Material and plating

Connector parts

Center conductor - plug
Center conductor - jack
Outer conductor
Coupling nut
Dielectric
Substrate

Material

CuBe
CuBe
Stainless steel
Stainless steel
PEEK
Al₂O₃

Plating

Gold, min. 1.27 µm, over nickel
Gold, min. 1.27 µm, over nickel
Passivated
Passivated

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/09.14/6.2

Technical Data Sheet				Rosenberger											
RPC-3.50		Attenuator Plug/Jack		03AS102-K10S3											
Electrical data Impedance Frequency range Return loss Attenuation Power handling 50 Ω DC to 26.5 GHz ≥ 26.4 dB, DC to 4 GHz ≥ 23.1 dB, 4 GHz to 12.4 GHz ≥ 19.1 dB, 12.4 GHz to 26.5 GHz 10 dB ± 0.5 dB, DC to 26.5 GHz 1 W at 25 °C															
Mechanical data Mating cycles Maximum torque Recommended torque Gauge ≥ 500 1.70 Nm 0.90 Nm 0.00 mm to 0.08 mm															
Environmental data Operating temperature range¹ Storage temperature range 0 °C to +50 °C - 40 °C to +85 °C RoHS compliant ¹ Temperature range over which these specifications are valid.															
Packing Standard Weight 1 pce in box 8.9 g/pce															
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.															
Draft		Date		Rev.		Engineering change number		Name		Date					
Kerstin Herzog		04.08.09		Markus Müller		25.10.16		f00		16-1390		Marion Striegler		25.10.16	
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de								Tel. : +49 8684 18-0 Email : info@rosenberger.de				Page 2 / 2			