


## RGA Series

### Features

- 105°C, 2,000 hours assured
- 105°C standard series for general purposes
- RoHS Compliance
- If there is any requirement on ESR, it's suggested to use low ESR series instead of RGA. Please consult us for any inquiry.




Sleeve & Marking Color: Black & White

### Specifications

Items	Performance																																																																																		
Category Temperature Range	6.3~400V	450V																																																																																	
	-40°C ~ +105°C	-25°C ~ +105°C																																																																																	
Capacitance Tolerance	±20% (at 120Hz, 20°C)																																																																																		
Leakage Current (at 20°C)	<table border="1"> <tr> <td>Rated voltage</td> <td>≤ 100V</td> <td>&gt; 100V</td> </tr> <tr> <td>Time</td> <td>after 2 minutes</td> <td>after 5 minutes</td> </tr> <tr> <td>Leakage Current</td> <td>I = 0.01CV or 3 (μA) whichever is greater</td> <td>CV ≤ 1,000 I = 0.03CV + 15(μA) CV &gt; 1,000 I = 0.02CV + 25(μA)</td> </tr> </table>		Rated voltage	≤ 100V	> 100V	Time	after 2 minutes	after 5 minutes	Leakage Current	I = 0.01CV or 3 (μA) whichever is greater	CV ≤ 1,000 I = 0.03CV + 15(μA) CV > 1,000 I = 0.02CV + 25(μA)																																																																								
	Rated voltage	≤ 100V	> 100V																																																																																
	Time	after 2 minutes	after 5 minutes																																																																																
	Leakage Current	I = 0.01CV or 3 (μA) whichever is greater	CV ≤ 1,000 I = 0.03CV + 15(μA) CV > 1,000 I = 0.02CV + 25(μA)																																																																																
Where, C = rated capacitance in μF V = rated DC working voltage in V																																																																																			
Tanδ (at 120 Hz, 20°C)	<table border="1"> <tr> <td>Rated Voltage</td> <td>6.3</td> <td>10</td> <td>16</td> <td>25</td> <td>35</td> <td>50</td> <td>63</td> <td>100</td> <td>160</td> <td>200</td> <td>250</td> <td>350</td> <td>400</td> <td>450</td> </tr> <tr> <td>Tanδ (max)</td> <td>0.23</td> <td>0.20</td> <td>0.16</td> <td>0.14</td> <td>0.12</td> <td>0.10</td> <td>0.09</td> <td>0.08</td> <td>0.12</td> <td>0.14</td> <td>0.17</td> <td>0.20</td> <td>0.25</td> <td>0.25</td> </tr> </table>		Rated Voltage	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450	Tanδ (max)	0.23	0.20	0.16	0.14	0.12	0.10	0.09	0.08	0.12	0.14	0.17	0.20	0.25	0.25																																																			
	Rated Voltage	6.3	10	16	25	35	50	63	100	160	200	250	350	400	450																																																																				
Tanδ (max)	0.23	0.20	0.16	0.14	0.12	0.10	0.09	0.08	0.12	0.14	0.17	0.20	0.25	0.25																																																																					
When the capacitance exceeds 1,000μF, 0.02 shall be added every 1,000μF increase.																																																																																			
Low Temperature Characteristics (at 120Hz)	Impedance ratio shall not exceed the values given in the table below.																																																																																		
	<table border="1"> <tr> <td colspan="2">Rated Voltage</td> <td>6.3</td> <td>10</td> <td>16</td> <td>25</td> <td>35</td> <td>50</td> <td>63</td> <td>100</td> <td>160</td> <td>200</td> <td>250</td> <td>350</td> <td>400</td> <td>450</td> </tr> <tr> <td rowspan="4">Impedance Ratio</td> <td>Z(-25°C)</td> <td>φ D &lt; 16</td> <td>4</td> <td>3</td> <td>3</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>2</td> <td>3</td> <td>6</td> <td>8</td> <td>12</td> <td>14</td> <td>16</td> </tr> <tr> <td>/Z(+20°C)</td> <td>φ D ≥ 16</td> <td>6</td> <td>4</td> <td>4</td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> <td>4</td> <td>8</td> <td>10</td> <td>16</td> <td>18</td> <td>-</td> </tr> <tr> <td>Z(-40°C)</td> <td>φ D &lt; 16</td> <td>8</td> <td>6</td> <td>6</td> <td>4</td> <td>4</td> <td>3</td> <td>3</td> <td>3</td> <td>4</td> <td>8</td> <td>10</td> <td>16</td> <td>18</td> <td>-</td> </tr> <tr> <td>/Z(+20°C)</td> <td>φ D ≥ 16</td> <td>12</td> <td>10</td> <td>8</td> <td>8</td> <td>8</td> <td>8</td> <td>6</td> <td>6</td> <td>4</td> <td>8</td> <td>10</td> <td>16</td> <td>18</td> <td>-</td> </tr> </table>		Rated Voltage		6.3	10	16	25	35	50	63	100	160	200	250	350	400	450	Impedance Ratio	Z(-25°C)	φ D < 16	4	3	3	2	2	2	2	2	3	6	8	12	14	16	/Z(+20°C)	φ D ≥ 16	6	4	4	3	3	3	3	3	4	8	10	16	18	-	Z(-40°C)	φ D < 16	8	6	6	4	4	3	3	3	4	8	10	16	18	-	/Z(+20°C)	φ D ≥ 16	12	10	8	8	8	8	6	6	4	8	10	16	18	-
	Rated Voltage		6.3	10	16	25	35	50	63	100	160	200	250	350	400	450																																																																			
	Impedance Ratio	Z(-25°C)	φ D < 16	4	3	3	2	2	2	2	2	3	6	8	12	14	16																																																																		
/Z(+20°C)		φ D ≥ 16	6	4	4	3	3	3	3	3	4	8	10	16	18	-																																																																			
Z(-40°C)		φ D < 16	8	6	6	4	4	3	3	3	4	8	10	16	18	-																																																																			
/Z(+20°C)		φ D ≥ 16	12	10	8	8	8	8	6	6	4	8	10	16	18	-																																																																			
* The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied with rated ripple current for 2,000 hours at 105°C.																																																																																			
Endurance	<table border="1"> <tr> <td>Test Time</td> <td>2,000 Hrs</td> </tr> <tr> <td>Capacitance Change</td> <td>Within ±20% of initial value</td> </tr> <tr> <td>Tanδ</td> <td>Less than 200% of specified value</td> </tr> <tr> <td>Leakage Current</td> <td>Within specified value</td> </tr> </table>		Test Time	2,000 Hrs	Capacitance Change	Within ±20% of initial value	Tanδ	Less than 200% of specified value	Leakage Current	Within specified value																																																																									
	Test Time	2,000 Hrs																																																																																	
	Capacitance Change	Within ±20% of initial value																																																																																	
	Tanδ	Less than 200% of specified value																																																																																	
Leakage Current	Within specified value																																																																																		
* The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied with rated ripple current for 2,000 hours at 105°C.																																																																																			
Shelf Life Test	<table border="1"> <tr> <td>Test Time</td> <td>1,000 Hrs</td> </tr> <tr> <td>Capacitance Change</td> <td>Within ±20% of initial value</td> </tr> <tr> <td>Tanδ</td> <td>Less than 200% of specified value</td> </tr> <tr> <td>Leakage Current</td> <td>Within specified value</td> </tr> </table>		Test Time	1,000 Hrs	Capacitance Change	Within ±20% of initial value	Tanδ	Less than 200% of specified value	Leakage Current	Within specified value																																																																									
	Test Time	1,000 Hrs																																																																																	
	Capacitance Change	Within ±20% of initial value																																																																																	
	Tanδ	Less than 200% of specified value																																																																																	
Leakage Current	Within specified value																																																																																		
* The above specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105°C without voltage applied. The rated voltage shall be applied to the capacitors before the measurements for 160 ~ 450V (Refer to JIS C 5101-4 4.1).																																																																																			
Ripple Current and Frequency Multipliers	<table border="1"> <tr> <td rowspan="2">Cap. (μF)</td> <td>Freq. (Hz)</td> <td>60 (50)</td> <td>120</td> <td>500</td> <td>1k</td> <td>10k up</td> </tr> <tr> <td>Under 100</td> <td>0.70</td> <td>1.00</td> <td>1.30</td> <td>1.40</td> <td>1.50</td> </tr> <tr> <td rowspan="2">100 &lt; C ≤ 1,000</td> <td>0.75</td> <td>1.00</td> <td>1.20</td> <td>1.30</td> <td>1.35</td> </tr> <tr> <td>1,000 up above</td> <td>0.80</td> <td>1.00</td> <td>1.10</td> <td>1.12</td> <td>1.15</td> </tr> </table>		Cap. (μF)	Freq. (Hz)	60 (50)	120	500	1k	10k up	Under 100	0.70	1.00	1.30	1.40	1.50	100 < C ≤ 1,000	0.75	1.00	1.20	1.30	1.35	1,000 up above	0.80	1.00	1.10	1.12	1.15																																																								
	Cap. (μF)	Freq. (Hz)		60 (50)	120	500	1k	10k up																																																																											
		Under 100	0.70	1.00	1.30	1.40	1.50																																																																												
	100 < C ≤ 1,000	0.75	1.00	1.20	1.30	1.35																																																																													
1,000 up above		0.80	1.00	1.10	1.12	1.15																																																																													

### Diagram of Dimensions




### Lead Spacing and Diameter

Unit: mm

φ D	5	6.3	8	10	12.5	16	18	22	25
P	2.0	2.5	3.5	5.0	5.0	7.5	7.5	10	12.5
φ d	0.5		0.6			0.8		1.0	
α	L < 20: 1.5, L ≥ 20: 2.0								2.0
β	0.5								

The case size of 12.5×16, 16×16, 16×20, 18×16, 18×20 and 18×25 are suitable for below diagram:



All product specifications in the catalog are subject to change without notice. (CAT. 2019E1)

Dimension:  $\phi D \times L$ (mm)

Ripple Current: mA/rms at 120 Hz, 105°C

### Dimension and Permissible Ripple Current

Cap.( $\mu$ F)	Rated Volt. (V <sub>DC</sub> ) Contents	6.3V (0J)		10V (1A)		16V (1C)		25V (1E)		35V (1V)		50V (1H)		63V (1J)		100V (2A)	
		$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
2.2	2R2											5×11	20			5×11	30
3.3	3R3											5×11	30			5×11	31
4.7	4R7											5×11	33			5×11	36
10	100											5×11	50			6.3×11	54
22	220											5×11	78	6.3×11	86	6.3×11	93
33	330									5×11	75	5×11	90	6.3×11	100	8×11.5	130
47	470							5×11	97	5×11	90	6.3×11	120	6.3×11	130	10×12.5	165
100	101					5×11	110	6.3×11	142	6.3×11	150	8×11.5	188	10×12.5	235	10×20	265
220	221	5×11	140	6.3×11	175	6.3×11	190	8×11.5	236	8×11.5	270	10×12.5	300	10×16	335	12.5×25	440
330	331			6.3×11	200	8×11.5	270	8×11.5	310	10×12.5	350	10×16	410	10×20	510	16×25	620
470	471	6.3×11	230	8×11.5	290	8×11.5	310	10×12.5	380	10×16	460	10×20	530	12.5×20	640	16×31.5	715
1,000	102	8×11.5	380	10×12.5	460	10×16	560	10×20	680	12.5×20	810	12.5×25	950	16×16	665	18×25	745
2,200	222	10×16	690	10×20	760	12.5×16	780	12.5×25	1,110	16×25	1,260	16×35.5	1,470	18×20	1,110	18×40	2,280
3,300	332	10×20	840	12.5×20	1,100	12.5×25	1,170	16×25	1,440	16×31.5	1,420	18×35.5	1,770	18×25	1,570	22×40	2,510
4,700	472	12.5×20	1,090	16×16	1,010	16×16	940	18×20	1,220	18×25	1,570	18×35.5	1,770	18×25	1,570	25×40	3,000
6,800	682	12.5×25	1,460	16×20	1,270	16×31.5	1,930	16×40	2,000	18×40	2,250	25×40	2,530	16×20	1,190		
10,000	103	16×20	1,340	16×31.5	2,220	18×20	1,585	18×35.5	2,160								
15,000	153	16×31.5	2,365	18×25	2,290	18×31.5	2,330	18×45	2,410	18×40	2,950	25×40	3,200				
22,000	223	16×40	2,800	18×35.5	2,930	18×40	3,230	22×40	3,460								
33,000	333	18×45	3,080	22×40	4,090	25×45	4,500										

Cap.( $\mu$ F)	Rated Volt. (V <sub>DC</sub> ) Contents	160V (2C)		200V (2D)		250V (2E)		350V (2V)		400V (2G)		450V (2W)	
		$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA	$\phi D \times L$	mA
1	010									6.3×11	21	8×11.5	27
2.2	2R2			6.3×11	30	6.3×11	35	6.3×11	35	8×11.5	39	8×11.5	39
3.3	3R3			6.3×11	39	6.3×11	40	8×11.5	43	8×11.5	45	8×11.5	45
4.7	4R7			6.3×11	43	8×11.5	45	8×11.5	45	8×11.5	50	8×11.5	50
10	100	8×11.5	65	8×11.5	65	10×12.5	92	10×16	95	10×16	95	10×20	105
22	220	10×12.5	110	10×16	140	10×16	140	12.5×20	220	12.5×20	160	12.5×20	160
33	330	10×16	150	10×20	170	12.5×16	175	12.5×25	215	16×20	225	16×20	225
47	470	10×20	195	12.5×16	215	12.5×20	230	16×16	205	16×20	255	16×25	295
68	680	12.5×20	275	16×16	290	16×20	320	18×25	360	18×25	360	16×35.5	400
100	101	12.5×25	355	16×20	365	18×20	415	16×31.5	370	16×31.5	375	18×31.5	420
150	151	16×25	470	18×16	360	16×25	425	18×20	460	18×35.5	540	18×40	560
220	221	16×31.5	660	18×20	510	16×31.5	550	18×25	535	18×40	600	22×40	730
330	331	18×35.5	820	18×31.5	750	18×35.5	760	25×40	865	22×45	930		
470	471	22×40	1,130	18×40	965	22×40	1,140	25×45	1,070				

### Part Numbering System

RGA Series    470 $\mu$ F     $\pm$ 20%    6.3V    Bulk Package    Gas Type    6.3  $\phi$  × 11L    Pb-free and PET sleeve

**RGA**    **471**    **M**    **0J**    **BK**    -    **0611**    **S**

Series Name    Capacitance    Capacitance Tolerance    Rated Voltage    Lead Configuration & Package    Rubber Type    Case Size    Lead Wire and Sleeve type    Supplement Code

Note: For more details, please refer to "Part Numbering System (Radial Type)".