

NOTES: UNLESS OTHERWISE SPECIFIED


1. P/N: 0268 & P/N: 0148/0
INSULATOR: HEAT SHRINK TUBING 221. BLACK.

BODY: BRASS. 100 TO 160μ [2.54 TO 4.06 μm] TIN PLATED.

CONTACT: COPPER ALLOY. 100 TO 160μ [2.54 TO 4.06 μm] TIN PLATED.
SPRING: COPPER ALLOY.

3. P/N W-700/COLOR
28AWG 7x36 TINNED COPPER
0.035 [0.89] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.

4. PERFORMANCE:
MAXIMUM CURRENT: 1.0 AMPS
MAXIMUM VOLTAGE: 600 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED

	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±	CONTRACT NO.		E-Z-HOOK[®] DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A.	
		APPROVALS	DATE		
		DRAWN R.L.	9/10		
	MATERIAL SEE NOTE.	APPROVED BY			
				DESCRIPTION E-Z-LINK 0.025" [0.63] SQ. SKT CONT. JUMPER	
	FINISH SEE NOTE.				
NEXT ASSY	USED ON			SIZE CODE IDENT NO. DRAWING NO.	
				A 08505 LT	
				SCALE 1:1	
APPLICATION	DO NOT SCALE DRAWING			SHEET 1 OF 1	

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-Z-HOOK. THE INFORMATION IS NOT TO BE REPRODUCED WITHOUT PRIOR WRITTEN PERMISSION OF E-Z-HOOK. DIV. OF TEKTEST INC.
MAXIMUM TESTED RATINGS IN A HANDS-FREE CONTROLLED ENVIRONMENT. MAXIMUM RATINGS ARE NOT TO BE USED CONCURRENTLY.