

2MN6

M

DRAWING
NUMBER

ISSUE

6

REPLACES

RELEASE NO.

CHECK

REVISIONS

A CO15200

WE 6

22 JUNE 65

B CO23123

ORD

21 MAR 68

C CO23152

QES

11 FEB 69

D CO 57992

M A M

24 SEP 85

CHECK

22 JUN 65

CHECK

22 JUN 65

CHECK

22 JUN 65

CHECK

22 JUN 65

CHECK

22 JUN 65

CHECK

22 JUN 65

CHECK

22 JUN 65

CHECK

22 JUN 65

CHECK

22 JUN 65





CHECK

22 JUN 65

CHECK


22 JUN 65

CHECK



NOTE-

1 - MOUNTING HOLES WILL ACCEPT NO.4 SCREWS ON
 .875 ± .003 AND 1.250 ± .003 CENTER



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE --- 16-24 OZ
 RELEASE FORCE --- 10 OZ MIN
 DIFFERENTIAL TRAVEL ----- .011 - .020
 OVERTRAVEL --- .017 MIN
 RELEASE TRAVEL ----- .022 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
 SEE CIRCUIT DIAGRAM

10 A-120, 240, OR 480 VAC; 1/2 HP-120 VAC
 1 HP-240 VAC; 0.8 A-115 VDC; 0.4 A-230 VDC
 0.1 A-550 VDC
 PILOT DUTY: 600 VAC MAX

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
 NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ±.030
 TWO PLACE (.00) ±.015
 THREE PLACE (.000) ±.005
 ANGLES ±

WEIGHT