




- 1 0.38 μ m [$.000015$] MIN GOLD ON MATING AREA,
1.27 μ m [$.000050$] MIN BRIGHT TIN-LEAD ON CRIMP AREA, BOTH OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 2 2.54 μ m [$.000100$] MIN BRIGHT TIN-LEAD, OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 3 GOLD FLASH ON CRIMP AREA,
2.54 μ m [$.000100$] MIN TIN ON MATING AREA, BOTH OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 4 0.38 μ m [$.000015$] MIN GOLD ON MATING AREA,
GOLD FLASH ON CRIMP AREA, BOTH OVER
1.27 μ m [$.000050$] MIN NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 6 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL

5 OBSOLETE	4	487923-5
3 6		487923-4
5 OBSOLETE	1	487923-3
2		487923-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.OBERMAN 3-7-90	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK R.STONE 3-8-90				
		APVD -	NAME			
		PRODUCT SPEC -	CONTACT, SOLDER TAB, .050 C/L			
MATERIAL PHOSPHOR BRONZE		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm$ - 1 PLC $\pm$ - 2 PLC $\pm$ 0.13 [$.005$] 3 PLC $\pm$ - 4 PLC $\pm$ - ANGLES $\pm$ -	APPLICATION SPEC -			
		FINISH SEE TABLE	WEIGHT -			
		CUSTOMER DRAWING		SIZE A2	CAGE CODE 00779	DRAWING NO C-487923
				SCALE 10:1	SHEET 1 OF 1	REV D1