

**EMDS13D2J-13.513M**
[Click part number to visit Part Number Details page](#)
**REGULATORY COMPLIANCE** (Data Sheet downloaded on Apr 6, 2019)
[Click badges to download compliance docs](#)

Regulatory Compliance standards are subject to updates by governing bodies. Click the badges to download the latest compliance docs for this part number directly from Ecliptek.

**ITEM DESCRIPTION**

MEMS Clock Oscillators LVDS (DS) 3.3Vdc 6 Pad 5.0mm x 7.0mm Plastic Surface Mount (SMD) 13.513MHz  $\pm 50$ ppm over 0°C to +70°C

**ELECTRICAL SPECIFICATIONS**

|                                                   |                                                                                                                                                                                                                                                                  |
|---------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nominal Frequency                                 | 13.513MHz                                                                                                                                                                                                                                                        |
| Frequency Tolerance/Stability                     | $\pm 50$ ppm Maximum over 0°C to +70°C (Inclusive of all conditions: Calibration Tolerance at 25°C, Frequency Stability over the Operating Temperature Range, Supply Voltage Change, Output Load Change, First Year Aging at 25°C, Reflow, Shock, and Vibration) |
| Aging at 25°C                                     | $\pm 1$ ppm Maximum First Year                                                                                                                                                                                                                                   |
| Supply Voltage                                    | 3.3Vdc $\pm 10\%$                                                                                                                                                                                                                                                |
| Input Current                                     | 80mA Maximum (Excluding Load Termination Current)                                                                                                                                                                                                                |
| Output Voltage Logic High (Voh)                   | 1.425Vdc Typical                                                                                                                                                                                                                                                 |
| Output Voltage Logic Low (Vol)                    | 1.075Vdc Typical                                                                                                                                                                                                                                                 |
| Differential Output Error (dVod)                  | 50mVdc Maximum                                                                                                                                                                                                                                                   |
| Differential Output Voltage (Vod)                 | 247mVdc Minimum, 350mVdc Typical, 454mVdc Maximum                                                                                                                                                                                                                |
| Offset Voltage (Vos)                              | 1.125V Minimum, 1.250V Typical, 1.375V Maximum                                                                                                                                                                                                                   |
| Rise/Fall Time                                    | 225pSec Typical, 325pSec Maximum (Measured over 20% to 80% of waveform)                                                                                                                                                                                          |
| Duty Cycle                                        | 50 $\pm 5$ (%) (Measured at 50% of waveform)                                                                                                                                                                                                                     |
| Offset Error (dVos)                               | 50mVdc Maximum                                                                                                                                                                                                                                                   |
| Load Drive Capability                             | 100 Ohms Between Output and Complementary Output                                                                                                                                                                                                                 |
| Output Logic Type                                 | LVDS                                                                                                                                                                                                                                                             |
| Logic Control / Additional Output                 | Standby (ST) and Complementary Output                                                                                                                                                                                                                            |
| Output Control Input Voltage                      | Vih of 70% of Vdd Minimum or No Connect to Enable Output and Complementary Output, Vil of 30% of Vdd Maximum to Disable Output and Complementary Output (High Impedance)                                                                                         |
| Standby Current                                   | 30 $\mu$ A Maximum (Without Load)                                                                                                                                                                                                                                |
| Period Jitter (Deterministic)                     | 0.2pSec Typical                                                                                                                                                                                                                                                  |
| Period Jitter (Random)                            | 2.0pSec Typical                                                                                                                                                                                                                                                  |
| Period Jitter (RMS)                               | 1.8pSec Typical, 2.5pSec Maximum                                                                                                                                                                                                                                 |
| Period Jitter (pk-pk)                             | 25pSec Typical, 30pSec Maximum                                                                                                                                                                                                                                   |
| RMS Phase Jitter (Fj = 637kHz to 10MHz; Random)   | 2.1pSec Typical                                                                                                                                                                                                                                                  |
| RMS Phase Jitter (Fj = 1MHz to 20MHz; Random)     | 1.7pSec Typical                                                                                                                                                                                                                                                  |
| RMS Phase Jitter (Fj = 1.875MHz to 20MHz; Random) | 1.5pSec Typical                                                                                                                                                                                                                                                  |
| Start Up Time                                     | 10mSec Maximum                                                                                                                                                                                                                                                   |
| Storage Temperature Range                         | -55°C to +125°C                                                                                                                                                                                                                                                  |

**ENVIRONMENTAL & MECHANICAL SPECIFICATIONS**

|                            |                                                |
|----------------------------|------------------------------------------------|
| ESD Susceptibility         | MIL-STD-883, Method 3015, Class 2, HBM 2000V   |
| Flammability               | UL94-V0                                        |
| Mechanical Shock           | MIL-STD-883, Method 2002, Condition G, 30,000G |
| Moisture Resistance        | MIL-STD-883, Method 1004                       |
| Moisture Sensitivity Level | J-STD-020, MSL 1                               |


**EMDS13D2J-13.513M**[Click part number to visit  
Part Number Details page](#)**ENVIRONMENTAL & MECHANICAL SPECIFICATIONS CONTINUED**

|                                     |                                                                   |
|-------------------------------------|-------------------------------------------------------------------|
| <b>Resistance to Soldering Heat</b> | MIL-STD-202, Method 210, Condition K                              |
| <b>Resistance to Solvents</b>       | MIL-STD-202, Method 215                                           |
| <b>Solderability</b>                | MIL-STD-883, Method 2003 (Six I/O Pads on bottom of package only) |
| <b>Temperature Cycling</b>          | MIL-STD-883, Method 1010, Condition B                             |
| <b>Thermal Shock</b>                | MIL-STD-883, Method 1011, Condition B                             |
| <b>Vibration</b>                    | MIL-STD-883, Method 2007, Condition A, 20G                        |

EMDS13D2J-13.513M

[Click part number to visit Part Number Details page](#)

MECHANICAL DIMENSIONS (all dimensions in millimeters)




| PIN | CONNECTION           |
|-----|----------------------|
| 1   | Standby (ST)         |
| 2   | No Connect           |
| 3   | Case Ground          |
| 4   | Output               |
| 5   | Complementary Output |
| 6   | Supply Voltage       |

| LINE | MARKING                                                             |
|------|---------------------------------------------------------------------|
| 1    | XXXX or XXXXX<br>XXXX or XXXXX=Ecliptek<br>Manufacturing Identifier |

Note A: Center paddle is connected internally to oscillator ground (Pad 3).

Suggested Solder Pad Layout

All Dimensions in Millimeters





All Tolerances are ±0.1

EMDS13D2J-13.513M

[Click part number to visit Part Number Details page](#)

OUTPUT WAVEFORM & TIMING DIAGRAM



**Test Circuit for Standby (Pad 1) and Complementary Output**


Note 1: An external 0.01µF ceramic bypass capacitor in parallel with a 0.1µF high frequency ceramic bypass capacitor close (less than 2mm) to the package ground and supply voltage pin is required.

Note 2: A low capacitance (<12pF), 10X attenuation factor, high impedance (>10Mohms), and high bandwidth (>500MHz) passive probe is recommended.

Note 3: Test circuit PCB traces need to be designed for a characteristic line impedance of 50 ohms.

EMDS13D2J-13.513M

[Click part number to visit Part Number Details page](#)

Recommended Solder Reflow Methods



High Temperature Infrared/Convection

|                                                                        |                                      |
|------------------------------------------------------------------------|--------------------------------------|
| <b><math>T_S \text{ MAX}</math> to <math>T_L</math> (Ramp-up Rate)</b> | 3°C/Second Maximum                   |
| <b>Preheat</b>                                                         |                                      |
| - Temperature Minimum ( $T_S \text{ MIN}$ )                            | 150°C                                |
| - Temperature Typical ( $T_S \text{ TYP}$ )                            | 175°C                                |
| - Temperature Maximum ( $T_S \text{ MAX}$ )                            | 200°C                                |
| - Time ( $t_s \text{ MIN}$ )                                           | 60 - 180 Seconds                     |
| <b>Ramp-up Rate (<math>T_L</math> to <math>T_P</math>)</b>             | 3°C/Second Maximum                   |
| <b>Time Maintained Above:</b>                                          |                                      |
| - Temperature ( $T_L$ )                                                | 217°C                                |
| - Time ( $t_L$ )                                                       | 60 - 150 Seconds                     |
| <b>Peak Temperature (<math>T_P</math>)</b>                             | 260°C Maximum for 10 Seconds Maximum |
| <b>Target Peak Temperature (<math>T_P \text{ Target}</math>)</b>       | 250°C +0/-5°C                        |
| <b>Time within 5°C of actual peak (<math>t_P</math>)</b>               | 20 - 40 Seconds                      |
| <b>Ramp-down Rate</b>                                                  | 6°C/Second Maximum                   |
| <b>Time 25°C to Peak Temperature (<math>t</math>)</b>                  | 8 Minutes Maximum                    |
| <b>Moisture Sensitivity Level</b>                                      | Level 1                              |

EMDS13D2J-13.513M

[Click part number to visit Part Number Details page](#)

Recommended Solder Reflow Methods



Low Temperature Infrared/Convection 240°C

|                                     |                                                        |
|-------------------------------------|--------------------------------------------------------|
| Ts MAX to TL (Ramp-up Rate)         | 5°C/Second Maximum                                     |
| Preheat                             |                                                        |
| - Temperature Minimum (Ts MIN)      | N/A                                                    |
| - Temperature Typical (Ts TYP)      | 150°C                                                  |
| - Temperature Maximum (Ts MAX)      | N/A                                                    |
| - Time (ts MIN)                     | 60 - 120 Seconds                                       |
| Ramp-up Rate (TL to TP)             | 5°C/Second Maximum                                     |
| Time Maintained Above:              |                                                        |
| - Temperature (TL)                  | 150°C                                                  |
| - Time (tL)                         | 200 Seconds Maximum                                    |
| Peak Temperature (TP)               | 240°C Maximum                                          |
| Target Peak Temperature (TP Target) | 240°C Maximum 2 Times / 230°C Maximum 1 Time           |
| Time within 5°C of actual peak (tp) | 10 Seconds Maximum 2 Times / 80 Seconds Maximum 1 Time |
| Ramp-down Rate                      | 5°C/Second Maximum                                     |
| Time 25°C to Peak Temperature (t)   | N/A                                                    |
| Moisture Sensitivity Level          | Level 1                                                |

Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum.

High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum.