





view shown without plastic pin



PC card drilling dimensions(after plating)
(thickness 1.60 or 2.40±0.20mm)



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D ±0.25	E±0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 ±0.15	D09P82C4PA00	D09P82C6PA00
15	39.14	33.32	26.32	25.12	19.18	5.90 ±0.15	D15P82C4PA00	D15P82C6PA00
25	53.03	47.04	40.04	38.84	33.12	5.70 ±0.25	D25P82C4PA00	D25P82C6PA00
37	69.32	63.50	56.50	55.30	49.68	5.70 ±0.25	D37P82C4PA00	D37P82C6PA00
							Gold flash	0.76 μ gold

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D ±0.25	E±0.07	G	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 ±0.15	D09P82C4PA00LF	D09P82C6PA00LF
15	39.14	33.32	26.32	25.12	19.18	5.90 ±0.15	D15P82C4PA00LF	D15P82C6PA00LF
25	53.03	47.04	40.04	38.84	33.12	5.70 ±0.25	D25P82C4PA00LF	D25P82C6PA00LF
37	69.32	63.50	56.50	55.30	49.68	5.70 ±0.25	D37P82C4PA00LF	D37P82C6PA00LF
							Gold flash	0.76 μ gold

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302	ISO 406 ISO 1101		D-SUB		
ltr	ecn no	dr	date	tolerances unless otherwise specified		MM	title		
G	ELX-I-18050	MP	2014/06/23	angles	linear		MALE CONNECTOR DELTA-D EUROSTYLE RIGHT ANGLED PRESS FIT		
				0°±2°					
						scale 2:1	dwg no	sheet 1 of 1	size
				dr	PESSON	1995/10/16	C01-8646-0384		
				enr	MITHUN PAUL	2014/06/23			
				chr	ALIAS BABU	2014/06/23	Product Customer Drawing		
				app	BIJU K PAUL	2014/06/23			
sheet index	revision sheet	G	1						