

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

47272-0023

Status:

Active

Overview:

DisplayPort® Cables and Connectors

Description:

0.50mm Pitch DisplayPort® Male Receptacle, Right Angle, SMT, 0.76µm Gold (Au) Plating, 20 Circuits, without Cover; with Mylar, Latch Holes, Flange, Peg and SMT Tab of Shell, Lead-Free

Documents:	
3D Model	Product Specification PS-47272-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	I/O Connectors
Series	47272
Application	Wire-to-Board
Comments	SMT Peg of Shell
Component Type	Receptacle
Overview	DisplayPort® Cables and Connectors
Product Name	DisplayPort®
Type	N/A
UPC	883906100704
Physical	
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
Flammability	94V-0
Gender	Male
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Bismuth
Material - Resin	High Temperature Thermoplastic
Net Weight	2.800/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Panel Mount	With Flange
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.762µm
Plating min - Termination	1.016µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-20°C to +85°C
Termination Interface: Style	Surface Mount
Waterproof / Dustproof	No

Electrical



image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

47272Series

Mates With

47271 Plug Sub-Assemblies, 68783 Cable Series

Current - Maximum per Contact	0.5A
Grounding to Panel	Yes
Shielded	Yes
Voltage - Maximum	40V AC

Solder Process Data

Duration at Max. Process Temperature (seconds)	3
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	250

Material Info

Reference - Drawing Numbers

Product Specification	PS-47272-001
Sales Drawing	SD-47272-001

* DisplayPort is a Trademark of VESA

This document was generated on 02/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION