

ALUMINUM ELECTROLYTIC CAPACITORS

KA series For High Grade Audio Equipment, Wide Temperature Range.




NEW

- 105°C high quality capacitors for audio equipment.
- Selected materials to create superior acoustic sound.
- Compliant to the RoHS directive (2002/95/EC).

KA




KT



Specifications

Item	Performance Characteristics							
Category Temperature Range	− 55 to +105°C							
Rated Voltage Range	6.3 to 50V							
Rated Capacitance Range	22 to 22000μF							
Capacitance Tolerance	±20% at 120Hz, 20°C							
Leakage Current	After 1 minute's application of rated voltage, leakage current is not more than 0.03CV or 4 (μA), whichever is greater. After 2 minutes' application of rated voltage, leakage current is not more than 0.01CV or 3 (μA), whichever is greater.							
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz at 20°C							
	Rated voltage (V)	6.3	10	16	25	35	50	
	tan δ (MAX.)	0.30	0.26	0.22	0.18	0.16	0.14	
	For capacitors with more than 1000μF, add 0.02 for every increase of 1000μF.							
Stability at Low Temperature	Measurement frequency : 120Hz							
	Rated voltage (V)		6.3	10	16	25	35	50
	tan δ (MAX.)	Z−25°C / Z+20°C	5	4	3	2	2	2
		Z−40°C / Z+20°C	10	8	6	4	3	3
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 105°C.				Capacitance Change		Within ± 20% of the initial capacitance value	
					tan δ		200% or less than the initial specified value	
					Leakage current		Less than or equal to the initial specified value	
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.							
Marking	Printed with black color letter on pearl blue sleeve.							

Radial Lead Type



Type numbering system (Example : 16V 1000µF)

1	2	3	4	5	6	7	8	9	10	11
U	K	A	1	C	1	0	2	M	P	D
			Capacitance tolerance (±20%)		Rated capacitance (1000µF)		Rated voltage (16V)		Series name	
									Type	
									Configuration	
									φ D	
									Pb-free leadwire	
									Pb-free PET sleeve	
									5	
									6.3	
									8-10	
									12.5 to 18	

Dimensions

Cap (µF)	V	6.3	10	16	25	35	50
Code	0J	1A	1C	1E	1V	1H	
22	220	5 × 11	45	5 × 11	54	5 × 11	68
33	330	5 × 11	55	5 × 11	65	5 × 11	90
47	470	5 × 11	65	5 × 11	79	5 × 11	115
100	101	5 × 11	95	5 × 11	115	6.3 × 11	190
220	221	6.3 × 11	160	6.3 × 11	190	8 × 11.5	300
330	331	6.3 × 11	195	8 × 11.5	265	10 × 12.5	410
470	471	8 × 11.5	270	8 × 11.5	315	10 × 16	530
1000	102	10 × 12.5	420	10 × 16	560	12.5 × 25	1040
2200	222	10 × 20	710	12.5 × 20	920	12.5 × 31.5	1470
3300	332	12.5 × 20	910	12.5 × 25	1050	12.5 × 35.5	1770
4700	472	12.5 × 25	1120	12.5 × 35.5	1300	16 × 31.5	
6800	682	12.5 × 35.5	1360	12.5 × 40	1570	18 × 35.5	
10000	103	12.5 × 40	1650	16 × 35.5	1890		
15000	153	16 × 35.5	2010	18 × 40	2400		
22000	223	18 × 40	2350				
							Case size φD × L (mm)
							Rated ripple

Frequency coefficient of rated ripple current

Cap. (µF)	Frequency	50Hz	120Hz	300Hz	1kHz	10kHz or more
22 to 47		0.75	1.00	1.35	1.57	2.00
100 to 470		0.80	1.00	1.23	1.34	1.50
1000 to 22000		0.85	1.00	1.10	1.13	1.15

Rated ripple current (mA rms) at 105°C 120Hz

Design, Specifications are subject to change without notice.

NICHICON CORPORATION

2011.J

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nichicon:

[UKA0J101MDD1TD](#) [UKA0J102MPD1TD](#) [UKA0J103MHD](#) [UKA0J153MHD](#) [UKA0J220MDD1TD](#) [UKA0J221MED1TD](#)
[UKA0J222MPD1TD](#) [UKA0J223MHD](#) [UKA0J330MDD1TD](#) [UKA0J331MED1TD](#) [UKA0J332MHD1TO](#)
[UKA0J470MDD1TD](#) [UKA0J471MPD1TD](#) [UKA0J472MHD1TO](#) [UKA0J682MHD](#) [UKA1A101MDD1TD](#)
[UKA1A102MPD1TD](#) [UKA1A103MHD](#) [UKA1A153MHD](#) [UKA1A220MDD1TD](#) [UKA1A221MED1TD](#) [UKA1A222MHD](#)
[UKA1A330MDD1TD](#) [UKA1A331MPD1TD](#) [UKA1A332MHD1TO](#) [UKA1A470MDD1TD](#) [UKA1A471MPD1TD](#)
[UKA1A472MHD](#) [UKA1A682MHD](#) [UKA1C101MDD1TD](#) [UKA1C102MPD1TD](#) [UKA1C103MHD](#) [UKA1C220MDD1TD](#)
[UKA1C221MED1TD](#) [UKA1C222MHD1TO](#) [UKA1C330MDD1TD](#) [UKA1C331MPD1TD](#) [UKA1C332MHD](#)
[UKA1C470MDD1TD](#) [UKA1C471MPD1TD](#) [UKA1C472MHD](#) [UKA1C682MHD](#) [UKA1E101MED1TD](#)
[UKA1E102MPD1TD](#) [UKA1E220MDD1TD](#) [UKA1E221MPD1TD](#) [UKA1E222MHD](#) [UKA1E330MDD1TD](#)
[UKA1E331MPD1TD](#) [UKA1E332MHD](#) [UKA1E470MDD1TD](#) [UKA1E471MPD1TD](#) [UKA1E472MHD](#) [UKA1E682MHD](#)
[UKA1H101MPD1TD](#) [UKA1H102MHD](#) [UKA1H220MDD1TD](#) [UKA1H221MPD1TD](#) [UKA1H222MHD](#)
[UKA1H330MDD1TD](#) [UKA1H331MPD1TD](#) [UKA1H332MHD](#) [UKA1H470MED1TD](#) [UKA1H471MHD1TO](#)
[UKA1V101MED1TD](#) [UKA1V102MHD1TO](#) [UKA1V220MDD1TD](#) [UKA1V221MPD1TD](#) [UKA1V222MHD](#)
[UKA1V330MDD1TD](#) [UKA1V331MPD1TD](#) [UKA1V332MHD](#) [UKA1V470MDD1TD](#) [UKA1V471MPD1TD](#)
[UKA1V472MHD](#)