





SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



N=Number of poles



P.C.B LAYOUT



Material

- Terminal body
- (metal housing): Brass(CuZn)
- Terminal screw: Steel Zinc plating "-" slot type
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 250VAC
- Current rating: 16A
- Wire range:
 - Solid wire(AWG): 14-22
 - Stranded wire(AWG): 14-222
- Torque: 3.5Lb-In
- Screw: M3
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.5KV/1.5KV/2KV
- Operating temperature: -30°C to +105°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety approval:

RoHS Compliant

PART NUMBER:

OSTTAXX2161

No. of Poles

02 2 Poles
03 3 Poles
... ..
24 24 Poles

COLOR

0: Black
5: Green
6: Blue (Standard)
8: Grey



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

TITLE		OSTTA - 7.5mm series						
PART NO.		OSTTAXX2161			DWG NO.	OSTTAXX2161.DWG		
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
Shi Jun 2006.10.19		Marvin 2006.10.19	Marvin 2006.10.19	Marvin 2006.10.19			UNIT: mm	X. ±0.50
						SCALE: NONE	X.XX ±0.30	
						SHEET: 01/01	REV: D	X° ±1°