



















REF. TE TE NO.	INDICE DE REVISION REVISION NUMBER	COULEUR COLOR	TOLERANCE POUR DETROMPAGE: ±0.05 KEYING TOLERANCE
1801179-1	D	NOIR BLACK	 ECHELLE 2:1 (100) 5.65
1801179-2	D	BLEU BLUE	 ECHELLE 2:1 (110) 3.75
1801179-3	D	GRIS GREY	 ECHELLE 2:1 (120) 1.85
1801179-4	D	JAUNE YELLOW	 ECHELLE 2:1 (130) 0.15
1801179-5	D	VERT GREEN	 ECHELLE 2:1 (140) 1.95
1801179-6	D	MARRON BROWN	 ECHELLE 2:1 (150) 3.85
1801179-7	D	BLANC WHITE	 ECHELLE 2:1 (160) 1.15
1801179-8	D	ROUGE RED	 ECHELLE 2:1 (170) 1.15
1801179-9	D	ORANGE ORANGE	 ECHELLE 2:1

- NOTES/NOTES:
- 1- 1801179-1 REPRESENTE (COD. NOIR) / AS SHOWN (COD. BLACK)
- 2 REPERE ALVEOLES / CAVITY MARKING
- 3 LOGO TE / TE LOGO
- 4 DATE D'ASSEMBLAGE / ASSEMBLY DATE
- 5 CODE DU LIEU D'ASSEMBLAGE / ASSEMBLY LOCATION DATE
- E = EUROPE / EUROPE
- C = CHINE / CHINA
- M = MERCOSUR / MERCOSUR
- 6 NUMERO DE LA MACHINE D'ASSEMBLAGE / NUMBER ASSEMBLY LINE
- 7 REF. TE DE L'ASSEMBLAGE (RACINE) / TE ASSEMBLY NO (RACINE)
- 8 REF. TE DE L'ASSEMBLAGE (SUFFIXE) / TE ASSEMBLY NO (SUFFIX)
- 9 INDICE DE REVISION PRODUIT / PRODUCT REVISION NUMBER
- 10- PIECES A UTILISER AVEC VOIR TABLEAU "COMPOSANTS ASSOCIES" / MATED WITH : SEE TABLE "ASSOCIATED PARTS"
- 11 FORME OPTIONNELLE / OPTIONAL SHAPE



SECTION CABLE ADMISSIBLE PAR CONTACT / ACCEPTABLE CABLE SECTIONS PER CONTACT

La section des câbles utilisés doit être comprise entre 0,35 et 2mm² avec un diamètre d'isolant compris entre 1,40mm mini et 2,80mm Maxi / The cross-section of the cables used must be between 0,35 and 2mm² (with insulator diameter included between 1,40mm mini and 2,80mm Maxi)



CAPOT FIXE 3 VOIES - SORTIE GAUCHE/DROITE / FIXED COVER 3 WAYS - LEFT/RIGHT EXIT	POUR GAINÉ ANNELEE DE 6mm / FOR CORRUGATED TUBE OF 6mm	1801467-1
CAPOT FIXE 3 VOIES - SORTIE HAUT/BAS / FIXED COVER 3 WAYS - UP/DOWN EXIT	POUR GAINÉ ANNELEE DE 6mm / FOR CORRUGATED TUBE OF 6mm	1-1801467-1
CAPOT FIXE 3 VOIES - SORTIE AXIALE / FIXED COVER 3 WAYS - EXIT IN LINE	POUR GAINÉ ANNELEE DE 6mm / FOR CORRUGATED TUBE OF 6mm	1801168-5
CAPOT ROTATIF 90 DEG. 3 VOIES / ROTATIVE COVER 90 DEG. 3 WAYS	POUR GAINÉ ANNELEE DE 6mm / FOR CORRUGATED TUBE OF 6mm	1-1801468-1
CLIP 1.5 SENSOR 11 DORE Section 1.4 à 2mm² / RECEPTACLE 1.5 SENSOR 11 GOLD PLATED Section 1.4 to 2mm²	POUR GAINÉ ANNELEE DE 6mm / FOR CORRUGATED TUBE OF 6mm	1670328-1
CLIP 1.5 SENSOR 11 DORE Section 0.75 à 1mm² / RECEPTACLE 1.5 SENSOR 11 GOLD PLATED Section 0.75 to 1mm²	POUR GAINÉ ANNELEE DE 6mm / FOR CORRUGATED TUBE OF 6mm	1670326-1
CLIP 1.5 SENSOR 11 DORE Section 0.35 à 0.5mm² / RECEPTACLE 1.5 SENSOR 11 GOLD PLATED Section 0.35 to 0.5mm²	POUR GAINÉ ANNELEE DE 6mm / FOR CORRUGATED TUBE OF 6mm	1564724-1
OBTURATEUR "MINI-ETANCHE" / "MINI-ETANCHE" PLUGGING PIN	CAPOT (*) / COVER	1801468-1
PORTE-LANGUETTES 3 VOIES HP / 3 WAYS TAB CONNECTOR HP	SUPPORT ADAPTER	1801359-1
DESCRIPTION / TITLE	COMPOSANTS ASSOCIES / ASSOCIATED PARTS	TE NO / REF. TE

(*) : POUR LE CAPOT ROTATIF, PRENDRE : SUPPORT + CAPOT / FOR THE ROTATIVE COVER, TAKE: ADAPTER + COVER

JAUNE / YELLOW	ACIER INOX / STAINLESS STEEL	RESSORT (x2) / SPRING (x2)	7
VERT / GREEN	PA66-GF30 (MATIERE: HB) / (HB MATERIAL)	CHARIOT SPRING-LOCK / SPRING-LOCK SLIDE	6
VERT / GREEN	SILICONE LUBRIFIE A 5% ; DURETE 30 SHORE A / LUBRIFICATED SILICON TO 5% ; HARNESS 30 SH. A	JOINT GROMMET / GROMMET SEAL	5
NOIR / BLACK	PBT-GF15 (MATIERE: HB) / (HB MATERIAL)	GRILLE ARRIERE / REAR GRID	4
VERT / GREEN	SILICONE LUBRIFIE A 4% ; DURETE 50 SHORE A / LUBRIFICATED SILICON TO 4% ; HARNESS 50 SH. A	JOINT INTERFACIAL / INTERFACE SEAL	3
VOIR TABLEAU DES REF. / SEE TABLE OF PART NO	PBT-GF15 (MATIERE: HB) / (HB MATERIAL)	DOUBLE VERROUILLAGE / COUDEGE (VOIR TABLEAU DES REFS) / SECONDARY LOCKING / CODING (SEE TABLE OF PART NO)	2
NOIR / BLACK	PBT-GF15 (MATIERE: HB) / (HB MATERIAL)	BOITIER PORTE-CLIPS / RECEPTACLE HOUSING	1
COULEUR / COLOR	MATIERE / MATERIAL	DESCRIPTION / TITLE	REP. ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 15FEB2008	TE Connectivity	
DIMENSIONS: mm		CHK X. JODON 15FEB2008	NAME 3 WAYS RECEPTACLE CONNECTOR SL	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD X. ROUILLARD 15FEB2008	PORTE-CLIPS 3 Voies SL	
0 PLC ±	1 PLC ±0.2	PRODUCT SPEC	SYSTEME A RESSORT	
2 PLC ±	3 PLC ±	108-15378	SIZE CAGE CODE DRAWING NO	
4 PLC ±	ANGLES ±2°	411-15712	RESTRICTED TO	
MATERIAL SEE TABLE / VOIR TABLEAU	FINISH SEE TABLE / VOIR TABLEAU	WEIGHT 8,8g	A100779C=1801179	
CUSTOMER DRAWING		SCALE 3:1	SHEET 1 OF 1 REV F	