


LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
G	14				G	REV & REDRAWN PER 0720-0040-93	3-22-93	AMP DAP




METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	UL Listed
8HD AWG SOLID OR STRANDED	8HD AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
8HD AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP AMP 8HDW* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			330968		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			PART NO		
PRODUCT INFORMATION CENTER 1-800-522-6752			AMP Incorporated Harrisburg, PA 17105-3608		
TOOLING ASSISTANCE CENTER 1-800-722-1111			NAME TERMINAL, RING TONGUE, HEAVY DUTY, SOLISTRAND™		
1-800-526-5142			SIZE CAGE CODE DRAWING NO		
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.			C=330968		
MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX			SCALE 4:1		
VOLTAGE RATING: NOT APPLICABLE			SHEET 1 OF 1		
WIRE CROSS SECTIONAL AREA RANGE: 6.64-10.5MM² [13,100-20,800] CIR MILS SOLID OR STRANDED			CUSTOMER DRAWING		
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -			MATERIAL COPPER PER ASTM B-152 ANNEALED		
FINISH TIN PLATE 0.00254[.000100] MIN THK PER MIL-T-10727			DR 3-22-93 TA BRINKMAN CHK 3-22-93 DA PATTERSON APPD 3-22-93 DE MILLER APPD 3-22-93 JL MECKLEY PRODUCT SPEC APPLICATION SPEC WEIGHT		