

フラット防水リフトハンドル
WATERPROOF FLUSH LIFT HANDLES

A



クレモン

ローラー
締り特装密閉
ハンドルフリーザー
密閉平面
スイング

ギア式

平面
ハンドルポップ
ハンドルリフト
ハンドルアジャスト
ハンドル

ラッチ式

パネル穴明け寸法
Panel drilling dimensions作動例
Example of operation

ハンドルを収納すると扉を3mm締付けます。
Door is tightened 3mm when the handle is encased in the housing.

PAT.PEND.

A-244
亜鉛合金製

特徴 Feature

- 防水タイプ(Oリング・シートパッキン使用)
- パネル表面からの出っ張りが6mm、パネル取付け面からの奥行が28.5mmの薄型タイプ
- ハンドルの引き上げ操作時と回転操作時にクリック感があり確実な操作ができます。
- ハンドルを収納することにより止め金が3mmリフト。シールド効果が得られます。
- 特殊ロック機構で従来の不安要素(止め金のガタ・振動・ロッド棒の自重落下)を解消、確実な施錠が行えます。
- 右用
- Waterproof (Using O-ring and sheet packing)
- Thin type: projections on the panel surface are 6mm and a depth from the panel installing surface is 28.5mm.
- You can get the click-feeling when the handle is lifted and turned so a dependable operation is provided.
- The stopper plate will be lifted up 3mm when the handle is encased in the housing, providing excellent sealing effects.
- Special lock mechanism ensures locking while eliminating former disadvantages. (Stopper plate looseness, vibration, rod falling by itself etc.)
- The right-hand use.

仕様

- 製品質量: 510g
- 材質: 亜鉛合金 (ZDC)
- 表面仕上: サチライトクロムめっき (MZCr)
- 鍵番号: 0200
- 適用板厚: 0.6~3.2mm
- 付属品: キー2本・ビスセット・専用止め金

動作

1. キーで解錠する。
2. ボタンを押しハンドルをポップアップさせる。(締付け解除)
3. ハンドルを90°回転する。
4. 開扉

用途

- 情報通信機器 (デジタル装置・磁気ディスク装置)などのEMI防止用シールドラック・各種振動機器の扉

納期
備考

- 標準品...納期お問合せください
- 鍵なしはお問合せください。
- 標準品は右用にセットされています。左用を使用の際はお問合せください。
- 本製品の錠前はキー先端部での操作となります。

Specifications

- Mass: 510g
- Material: Zinc alloy (ZDC)
- Finish: Satellite chrome plating (MZCr)
- Key No.: 0200
- Applicable panel thickness: 0.6 to 3.2mm
- Accessories: Two keys, screws and special stopper plate

Operation


1. Unlock with a key.
2. Push the button and pop up the handle. (tightening is released)
3. Turn the handle 90°.
4. Open the door.

Specific use

- EMI prevention sealed racks for information and communication equipment (digital devices and magnetic disks) and doors for various vibration equipment

Remarks

- The lock on this product is operated with the tip of the key.

使用例
Example of application

商品番号 Product No.	RoHS 2D	CAD 2D/3D	備考 Remarks	コード Code	単価 Price	量販価格 Bulk Price 数量 Quantity	単価 Price
A-244-2-1	●	2D	鍵付き With lock	02242	¥4,100	5個~	¥3,936
A-244-2-2	●	2D/3D	鍵なし Without lock	02243	¥3,900	5個~	¥3,744

●: RoHS指令対応品
▲: RoHS指令に対応可能です。

※大量のご注文は更にお安くなります。