


DRAWING MADE IN AMERICAN PROJECTION

SHEET 1 OF 2

NUMBER
480727

1. MATES WITH CAP 480728
2. TO BE USED WITH MATE-N-LOK DUAL LANCE SOCKETS.
3. OPTIONAL CONSTRUCTION

HOUSING	MATERIAL	COLOR
1-480727-0	NYLON	NATURAL

DIMENSIONS IN INCHES. DO NOT SCALE PRINT.

Copyright © 1973 by AMP Incorporated. All rights reserved. AMP products covered by patents and/or patents pending.

© 1973 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

MATERIAL AND FINISH

SEE TABLE

AMP INCORPORATED
HARRISBURG, PENNA.

CLASS .084 SOCKET HOUSING

WIRE — RANGE — INSULATION
— H — — H —


TYPE PANEL MOUNT

TOLERANCE EXCEPT
AS NOTED
± .010SCALE
NTS

LOC. CM A NO. 480727

REV F

NAME 4 CIRCUIT MATE-N-LOK PLUG
DUAL LANCE HOUSING

NUMBER
480727.015 R MAX
ALL CORNERS

- NOTE: 1. Recommended panel thickness .025 - .065.
2. Both locking legs to be squeezed together and housing to be inserted straight-in, as opposed to a rocking manner of insertion.
3. The panel must be punched so that the housing enters the panel in the same direction as the punch.
4. Dimensions I and II to be equal within .005.
5. Panel must not have any material (paint, porcelain, etc.) applied in the mounting hole area that would decrease retention of the housing in the panel.
6. If Notes 3 and/or 5 are not complied with, the 1.100 dimension should be reduced to .080 to assure proper housing retention in the panel.

©1973 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

MATERIAL AND FINISH

H

WIRE RANGE INSULATION

TOLERANCE EXCEPT AS NOTED
± .005 ± .005SCALE
NTSLOC
CMNO SHEET 2 OF 2
480727REV
F

NAME
RECOMMENDED MOUNTING INFORMATION
4 CIRCUIT MATE-N-LOK PANEL MOUNT FLNG

CUSTOMER COPY
REFERENCE ONLY

AMP

AMP INCORPORATED
HARRISBURG, PENNA.

CLASS H

TYPE H

LTR REVISION RECORD

ETN

DATE

DR 1/1/73

DE

CHK 3/19/73

APP