








N=Number of poles



P.C.B LAYOUT

SIGN	DATE	DESCRIPTION	APPROVER
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

- Material
- Terminal body (Contact pin): Brass
 - Wire guard: Stainless steel
 - Surface of solder tail: Tin plated
 - Insulator (housing): Thermoplastic (UL94V-0)
- Electrical
- Voltage rating: AC 300V
 - Current rating: 10A
 - Wire range:
 - Solid wire(AWG): 16-26
 - Stranded wire(AWG): 16-26
 - Wire strip length: 7-8mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 250°C±10°C/5 Sec
 - Safety Approval: pending approval 
- RoHS Compliant

Part Number

OSTHXXX2181

- | | |
|--------------|--------------------|
| 01: 01 Poles | 0: Black |
| 02: 02 Poles | 2: Red |
| | 5: Green |
| 24: 24 Poles | 8: Grey (Standard) |
| | 9: White |
| | C: Multiple colors |

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.



TITLE		OSTHX 3.5 Series 90° single contact (Wire inlet)					
PART NO.		OSTHXXX2181		DWG NO.		OSTHXXX2181.DWG	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
						X.	±0.50
		kind 2008.7.22	kind 2008.7.22		SHEET: 01/01	UNIT: mm	X.X ±0.30
						SCALE: NONE	X.XX ±0.10
						REV: B	X° ±1°