





NOTES:

1. CPR IS 34dB ACCORDING TO IEEE DRAFT P802.3Z/D5.0
2. ATTENUATION $\leq 0,3\text{dB}$, MEASURED AT 1300nm
ACC. IEC 61300-3-4 METHOD B
3. FILLED OUT TEST RESULT SHEET IS SUPPLIED
WITH EACH INDIVIDUALLY PACKED ASSEMBLY
4. INDIVIDUAL LENGTH DIFFERENCE ON ST SIDE $\leq 50\text{mm}$ AND ON SC SIDE $\leq 5\text{mm}$
5. TEXT ON CABLE LABEL: "TO CABLE PLANT"
6. INFORMATION ON CABLE LABEL:
 - F.O. NUMBER
 - PRODUCTION DATE
7. TEXT ON CABLE LABEL: "MODE CONDITIONING CABLE ASSEMBLY"
8. INFORMATION ON CABLE LABEL:
 - BARCODE
 - UNIQUE SERIAL NUMBER
 - TYCO ELECTRONICS PART NUMBER
 - MANUFACTURING LOCATION
 - PRODUCTION DATE
9. TEXT ON CABLE LABEL: "TO EQUIPMENT"

PART NUMBER	"L" (meter)
6348271-2	2,2 -0/+0,1
6348271-3	3,2 -0/+0,1
6348271-4	4,2 -0/+0,1
6348271-5	5,2 -0/+0,1
6348271-6	6,2 -0/+0,1
6348271-7	7,2 -0/+0,1
6348271-8	8,2 -0/+0,1
6348271-9	9,2 -0/+0,1
1-6348271-0	10,2 -0/+0,1

5	FOAC CABLE LABEL	6
1	SC CONNECTOR SINGLE MODE, DUPLEX HOUSING, BLUE	5
1	SC CONNECTOR MULTI MODE, DUPLEX HOUSING, BEIGE	4
2	ST CONNECTOR MULTI MODE	3
1	CPR SLEEVE	2
1	FOCAB 2,5TZ 62.5/125 ORANGE LSZH	1
Qty	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24FEB2006 R. COOLEN CHK 24FEB2006 A. HENGMEULEN APVD 24FEB2006 T. vd. MEULEN PRODUCT SPEC 108-19168 APPLICATION SPEC — WEIGHT —	Tyco Electronics Corporation 's-Hertogenbosch, Netherlands NAME FOGBIT62.5 MCLL 2,5TZ 2x ST/PC — SC/PC DUPLEX SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C-6348271 —
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± ± — MATERIAL FINISH — —	CUSTOMER DRAWING SCALE NTS SHEET 1 OF 1 REV R1	