

Endicott Research Group, Inc.

2601 Wayne St., Endicott, NY 13760 607-754-9187 Fax 607-754-9255 http://www.ergpower.com

SFDMB3945F

Specifications and Applications Information

03/29/11


The ERG Smart Force Series of LED Drivers are specifically designed for applications which require high efficiency, small footprint and LCD brightness stability over a wide input voltage range. The SFDMB3945F is designed to provide backlight power for the NEC NL10276BC20-18 display.

Designed, manufactured and supported within the USA, the SFDM features:

- ✓ Less than 5 mm in height
- ✓ Wide input voltage range
- ✓ Constant LED current
- ✓ With external PWM dimming signal, up to 1000:1 dimming ratio
- ✓ Open and short circuit protection
- √ High efficiency
- ✓ Separate enable and dimming function
- ✓ Soft start
- ✓ One year warranty

	Connectors
Input Connector	Output Connector*
Molex 53261-0871	Molex 53261-0471
J1-1 Vin(+) J1-2 Vin(+) J1-3 GND J1-4 GND J1-5 Enable J1-6 PWM J1-7 N/C J1-8 Fault Indicator (output)	J2-1 Cathode 1 J2-2 Anode 1 J2-3 Cathode 2 J2-4 Anode 2 * Requires harness: ERG part number H11404152 recommended

Smart Force LED Driver





Absolute Maximum Ratings

Rating	Symbol	Value	Units
Input Voltage Range	V _{in}	-0.3 to +20.0	Vdc
Storage Temperature	T _{stg}	-40 to +85	°C
Enable Input Voltage	V _{Enable}	0 to Vin	Vdc
PWM Input Voltage	V _{PWM}	0 to +5.0	Vdc
Fault Indicator	V _{FL}	0 to +4.0	Vdc

Operating Characteristics

Unless otherwise noted Vin = 12.00 Volts dc and Ta = 25°C.

Characteristic	Symbol	Min	Тур	Max	Units
Input Voltage	V _{in}	+8.0	+12.0	+20.0	Vdc
Component Surface Temperature (Note 1)	T _s	-40	-	+80	°C
Input Current	I _{in}	0.30	0.35	0.40	Adc
LED String Voltage (Note 2)	V_{LED}	26.0 (Note 3)	-	38.5	Vdc
Efficiency (Note 4)	η	-	87	-	%
Output Current (per string)	I _{out}	57	60	63	mAdc
Enable Pin (Note 5)					
Turn-on Threshold	V _{thon}	-	-	3.5	Vdc
Turn-off Threshold	V _{thoff}	0.8	-	-	Vdc
Enable Input Impedance (Note 6)	R _{Enable}	-	9.0	-	kOhms
PWM Pin (Note 7)					
Turn-on Threshold	V _{thon}	-	-	2.0	Vdc
Turn-off Threshold	V _{thoff}	0.9	-	-	Vdc
PWM Input Impedance (Note 8)	R _{PWM}	-	9.0	-	kOhms
Frequency (Notes 9, 10)	F _{PWM}	130	-	40,000	Hz

(Operating Characteristics and notes are continued on next page.)



Note 4

Operating Characteristics (continued)

Characteristic	Symbol	Min	Тур	Max	Units
Fault Indicator					
No Fault Level (Note 11)	V _{NFL}	-	2.5	-	Vdc
Fault Level (Note 11)	V _{FL}	-	0.3	-	Vdc

Specifications subject to change without notice.

Note 1	Surface temperature must not exceed 80°C, except U1, which cannot exceed 95°C.
Note 2	Exceeding maximum string voltage specification will damage the LED driver.
Note 3	The LED driver is capable of driving strings less than the minimum string voltage specification,
	although doing so will limit the maximum input voltage.


To determine max Vin:

Efficiency is calculated using a 30.4V LED string.

 $\overline{minimum}$ LED string voltage ≥ (1.3) x (Vin maximum)

Note 5	The Enable pin is internally pulled up above the turn-on threshold.
Note 6	Enable pin input impedance is $9k\Omega$ to $10V$ with a $12V$ input voltage.
Note 7	PWM pin is internally pulled up above the turn-on threshold.
Note 8	PWM pin input impedance is $9k\Omega$ to 4V with a 12V input voltage.
Note 9	Operating outside of this frequency range may cause the driver to shut down or malfunction.
Note 10	Minimum pulse width required for reliable operation is 5µs.
Note 11	Loading with an impedance less than 100kQ to Vcc or to ground may cause the default levels to change





Application Information

The ERG SFDMB3945F has been designed to be configured in multiple ways:

NO DIMMING

- OPERATION: The SFD can be configured to operate without dimming by floating the Enable (J1-5) and PWM (J1-6) pins.
- Pins 1 and 2 of connector J1 must be connected to +Vin, between 8 and 20 Vdc. Pins 3 and 4 of connector J1 must be connected to GND.
- DISABLING DRIVER: Pulling the Enable pin (J1-5) below the minimum turn-off threshold of 0.8V will disable the driver. Disabling the driver will require the ability to sink ≥2mA below the turn-off threshold. This pin may be driven by an open collector stage or a totem pole stage.

EXTERNAL PWM DIMMING


- OPERATION: External PWM configuration as shown in Figure 1 allows the user to control display brightness
 with an externally generated PWM signal. The user is responsible to provide the PWM signal. A dimming ratio up
 to 1000:1 is possible with this configuration. The minimum pulse width is 5µs.
- DIMMING: Dimming is accomplished by applying a PWM signal to the PWM pin (J1-6). PWM on and off levels
 are specified in the Operating Characteristics section of the data sheet. Display brightness is modulated by
 controlling the PWM duty cycle as shown in Graph 1. Pin 6 may be driven by an open collector stage capable of
 sinking >1mA, or a totem pole stage.
- Pins 1 and 2 of connector J1 must be connected to +Vin, between 8 and 20 Vdc. Pins 3 and 4 of connector J1 must be connected to GND. Pin 5 must either be floating or above the full on threshold if being driven by a totem pole stage.
- DISABLING DRIVER: Pulling the Enable pin (J1-5) below the minimum turn-off threshold of 0.8V will disable the driver. Disabling the driver will require the ability to sink ≥2mA below the turn-off threshold. This pin may be driven by an open collector stage or a totem pole stage.

FAULT INDICATOR

• The Fault Indicator pin (J1-8) may be used as a feedback signal that will fall below the fault level of 0.3V in the case of an open string, a shorted string, an output overvoltage condition, or an over temperature condition. If used, this pin should be loaded with a high impedance stage as specified in the Operating Characteristics. Do not drive this pin with a voltage, as it will damage the driver.



EXTERNAL PWM DIMMING






Figure 1

(1) Low ESR type input by-pass capacitor (10 uF - 220 uF) may be required to reduce reflected ripple and to improve power supply response.



Endicott Research Group, Inc. (ERG) reserves the right to make changes in circuit design and/or specifications at any time without notice. Accordingly, the reader is cautioned to verify that data sheets are current before placing orders. Information furnished by ERG is believed to be accurate and reliable. However, no responsibility is assumed by ERG for its use.