

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 501)

PHYSICAL CHARACTERISTICS

-INSULATOR MATERIAL: THERMOPLASTIC UL94V0

-CONTACT MATERIAL: BRASS,
GOLD OVER NICKEL

-ACCESSORIES: BRASS,cadmium plated yellow passivation

-SHELLS: STEEL,cadmium plated yellow passivation

ELECTRICAL CHARACTERISTICS

-NOMINAL CURRENT: 7.5A

-CONTACT RESISTANCE: <= 7.3 m ohms

-CONTACT/CONTACT : >=1000 V

-CONTACT/GROUND : >=1200 V

-INSULATION RESISTANCE: >=5000 MOhms

ENVIRONMENTAL CHARACTERISTICS

- CLIMATIC CATEGORY: 55/125/56

TEMPERATURE RANGE -55°C TO +125°C

DAMP HEAT STEADY STATE 56 DAYS

SALT SPRAY 48 HOURS

MECHANICAL CHARACTERISTICS

- RETENTION AGAINST TORQUE: - Threaded insert: 0.7 N.m minimum

- Female screw : 0.5 N.m minimum

Series

DBML25P400

Shell size: **E A B C D**
see sheet 2

Front accessory definition
see sheet 2

Blank :without accessory

F :floating mounting

L :threaded insert M3

O :threaded insert UNC 4-40

V :female screw UNC 4-40

Contact number (see sheet 2)

9,15,25,37,50

Contacts

P :Pin


Termination type

4 3 level wire wrap contact

Plating

00 : 500 matings/unmatings

43 : 500 matings/unmatings for harsh environment



25 WAY for Example

rev	ecn no	dr	date
A	LS06-0174	MPE	2006/11/14
B	LS07-0273	MPE	2007/10/30
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com		surface	-	tolerance std	projection	mm	
		ISO 1302	✓	ISO 406	ISO 1101		
		TOLERANCES UNLESS OTHERWISE SPECIFIED					
		ANGULAR	LINEAR	0.X	±0.3	size	Scale
				0.XX	±0.1	A2	2:1
		0° ±2°		0.XXX	±0.05	ECN	LS07-0273
		Product family				Spec.ref	
		SUB MALE DM HE501 series				C01-8637-1739	Rev.
		with 3 level wire wrap contact				B	
		catalog no				CUSTOMER	sheet 1 of 4



Copyright FCI.

1 2 3 4 5 6 7 8

A


B

C

D

E

F



FRONT
ACCESSORY

Blank without

F floating mounting

L insert M3
O insert UNC 4.40

V female screw UNC 4.40

PART NUMBER	FRONT ACCESSORY
D*MxxP443	without
D*MFxxP443	floating mounting
D*MLxxP443	insert M3
D*MOxxP443	insert UNC 4.40
D*MVxxP443	female screw UNC 4.40

shell size	Contact number
X	XX
E	09
A	15
B	25
C	37
D	50

PART NUMBER	FRONT ACCESSORY
D*MxxP400	without
D*MFxxP400	floating mounting
D*MLxxP400	insert M3
D*MOxxP400	insert UNC 4.40
D*MVxxP400	female screw UNC 4.40

CROSS REFERENCES HE501 and FCI

HE501 P/N	FCI P/N	FRONT ACCESSORY
HE501NxxKP3	D*MxxP400	without
HE501FxxKP3	D*MFxxP400	floating mounting

SCALE: 4

www.fciconnect.com		surface -	tolerance std	projection	mm
		ISO 1302	ISO 406 ISO 1101	⊕	→
		TOLERANCES UNLESS OTHERWISE SPECIFIED		size	Scale
Dr	M PESSON	2006/11/14	ANGULAR	0.X ±0.3	A2 2:1
Eng	P LEGARE	2006/11/14	LINEAR	0.XX ±0.1	
Chr	P LEGARE	2006/11/14	0° ±2°	0.XXX ±0.05	ECN LS07-0273
Appr	P LEGARE	2006/11/14	Product family	-	Spec ref
FCI SUB MALE DM HE501 series		with 3 level wire wrap contact	catag no	deg no	Rev.
				C01-8637-1739	B
			CUSTOMER	sheet 2 of 4	

A

B

C

D

E


F



Copyright FCI.

REV 7 - 2006-04-17

1 2 3 4 5 6 7 8



www.fciconnect.com		surface	ISO 1302	tolerance std	ISO 406	ISO 1101	projection	mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	M PESSON	2006/11/14	ANGULAR	0.X	±0.3	size	A2	Scale
Eng	P LEGARE	2006/11/14	LINEAR	0.XX	±0.1	2:1		
Chr	P LEGARE	2006/11/14	0° ±2°	0.XXX	±0.05	ECN	LS07-0273	
Appr	P LEGARE	2006/11/14	Product family		Spec ref			
SUB MALE DM HE501 series		with 3 level wire wrap contact		C01-8637-1739		Rev.		B
catalog no				CUSTOMER		sheet 3 of 4		

