



MRO50-81037

High-pressure Desiccant Dehydrator, 19 in rack mountable, 3.0–5.0 psig, 10–72 Vdc

- To meet our global customer's RoHS environmental needs, we have changed our desiccant to a cobalt-chloride free desiccant. The compliant desiccant is orange when dry and turns green when saturated.

OBSOLETE

This product was discontinued on: October 27, 2016


Replaced By

HR150

Heat Regenerated Dehydrator, 19 in rack mountable, 3.0 kPa (0.44 psig), with summary alarms, 48 Vdc


MRO50-81037

Outline Drawing-Front




MRO50-81037

Outline Drawing-Side



MRO50-81037


Outline Drawing-Top



TOP VIEW

MRO50-81037

Outline Drawing-Section



Alarm

Low-Pressure Alarm	Factory set
--------------------	-------------

Dimensions

Net Weight	10.3 kg		22.6 lb
Product Depth	228.6 mm		9.0 in
Product Height	177.8 mm		7.0 in
Product Width	482.6 mm		19.0 in
Gross Weight, Packed	11.4 kg		25.1 lb
Product Depth, Packed	584.2 mm		23.0 in
Product Height, Packed	304.8 mm		12.0 in
Product Width, Packed	457.2 mm		18.0 in

Electrical Specifications

Power Cord	USA power cord
Voltage	10–72 Vdc ±10%
Power Consumption, average	11.0 W

General Specifications

Dehydrator Type	Desiccant
Voltage Type	dc
Volume Capacity, minimum	0.0 L 0.0 ft³

MRO50-81037

Volume Capacity, maximum	283.2 L 10.0 ft ³
Dew Point	-36 °C (-33 °F)
Flow Rate, nominal	0.05 SCFM 1.40 SLPM
Includes	3/8 in polyethylene tubing Drill template Instruction sheet Male connector fitting Power cord Power cord connector lock PTFE tape Screws Street tee fitting
Port Type	3/8 in PE tube
Rack Type	EIA 19 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system