

## IFM MAGNIFIERS



16346LG



16351LG

**IFM Magnifier** is the ideal light-duty magnifier for low-power inspection. With a sturdy, stamped steel shade, it features a 5" diameter, 3-diopter (1.75X) or 5-diopter (2.25X) lens and choice of 45" or 30" arm lengths. The IFM Magnifier is a smart, economical choice for tight budgets.

- 30" or 45" external spring arm.
- Clamp or base mount.
- 5" diameter, 3-diopter (1.75X) or 5-diopter (2.25X) lens housed in a stamped steel shade.
- Expanded model range.
- Lamp diffuser cover.
- 22-Watt circline fluorescent lamp provides 360° shadow-free illumination.
- Built-in starter switch.
- 3-wire cord.
- Operates on 120VAC.
- 30" arm models are available with a weighted base.
- 3-wire single outlet receptacle is provided at the base of the arm for models 16345WT and 16346WT.
- Electromagnetic ballast.
- UL/CUL listed.
- 5 year warranty.

### IFM Magnifiers

| Part No. | Description | Lens Type | Color  | Arm Length | Mounting Bracket |
|----------|-------------|-----------|--------|------------|------------------|
| I 6345   | IFM1A 3D    | 3-Diopter | LG, WT | 45"        | Edge Mount       |
| I 6346   | IFM1A 5D    | 5-Diopter | LG, WT | 45"        | Edge Mount       |
| I 6350   | IFM2A 3D    | 3-Diopter | LG     | 30"        | Edge Mount       |
| I 6351   | IFM2K 3D    | 3-Diopter | LG     | 30"        | Base Mount       |
| I 6352   | IFM2A 5D    | 5-Diopter | LG     | 30"        | Edge Mount       |
| I 6353   | IFM2K 5D    | 5-Diopter | LG     | 30"        | Base Mount       |

**NOTE:** Light Gray (LG), White (WT)

