

FG3300AH-50DA

HIGH POWER INVERTER USE
PRESS PACK TYPE


FG3300AH-50DA



- ITQRM Repetitive controllable on-state current3300A
- IT(AV) Average on-state current1000A
- VDRM Repetitive peak off state voltage2500V
- Anode short type

OUTLINE DRAWING

Dimensions in mm



APPLICATION

Inverters, D.C. choppers, Induction heaters, D.C. to D.C. converters.

MAXIMUM RATINGS





Symbol	Parameter	Voltage class	Unit
		50DA	
VRRM	Repetitive peak reverse voltage	17	V
VRSM	Non-repetitive peak reverse voltage	17	V
VR(DC)	DC reverse voltage	17	V
VDRM	Repetitive peak off-state voltage*	2500	V
VDSM	Non-repetitive peak off-state voltage*	2500	V
VD(DC)	DC off-state voltage*	2000	V

* : VGK = -2V

Symbol	Parameter	Conditions	Ratings	Unit
ITQRM	Repetitive controllable on-state current	V _{DM} = 1875V, T _J = 125°C, C _s = 6.0μF, L _s = 0.2μH	3300	A
IT(RMS)	RMS on-state current		1570	A
IT(AV)	Average on-state current	f = 60Hz, sine wave θ = 180°, T _r = 81°C	1000	A
ITSM	Surge (non-repetitive) on-state current	One half cycle at 60Hz	24	kA
I ² t	Current-squared, time integration	One cycle at 60Hz	2.4 × 10 ⁶	A ² s
diT/dt	Critical rate of rise of on-state current	V _D = 1250V, I _{GM} = 40A, T _J = 125°C	500	A/μs
VFGM	Peak forward gate voltage		10	V
VRGM	Peak reverse gate voltage		17	V
IFGM	Peak forward gate current		100	A
IRGM	Peak gate reverse current		1100	A
PFGM	Peak forward gate power dissipation		400	W
PRGM	Peak reverse gate power dissipation		27	kW
PFG(AV)	Average forward gate power dissipation		100	W
PRG(AV)	Average reverse gate power dissipation		230	W
T _J	Junction temperature		-40 ~ +125	°C
T _{stg}	Storage temperature		-40 ~ +150	°C
—	Mounting force required	Recommended value 33	30 ~ 40	kN
—	Weight	Standard value	1220	g

FG3300AH-50DAHIGH POWER INVERTER USE
PRESS PACK TYPE**ELECTRICAL CHARACTERISTICS**


Symbol	Parameter	Test conditions	Limits			Unit
			Min	Typ	Max	
V _{TM}	On-state voltage	T _j = 125°C, I _{TM} = 3300A, Instantaneous measurment	—	—	3.0	V
I _{RRM}	Repetitive peak reverse current	T _j = 125°C, V _{RRM} Applied	—	—	300	mA
I _{DRM}	Repetitive peak off-state current	T _j = 125°C, V _{DRM} Applied, V _{GK} = -2V	—	—	150	mA
I _{RG}	Reverse gate current	T _j = 125°C, V _{RG} = 17V	—	—	300	mA
dv/dt	Critical rate of rise of off-state voltage	T _j = 125°C, V _D = 1250V, V _{GK} = -2V	1000	—	—	V/μs
t _{gt}	Turn-on time	T _j = 125°C, I _{TM} = 3300A, I _{GM} = 40A, V _D = 1250V	—	—	10	μs
t _{gq}	Turn-off time	T _j = 125°C, I _{TM} = 3300A, V _{DM} = 1875V, diGQ/dt = -40A/μs V _{RG} = 17V, C _S = 6.0μF, L _S = 0.2μH	—	—	35	μs
I _{GQM}	Peak gate turn-off current		—	780	—	A
V _{GT}	Gate trigger voltage	DC METHOD : V _D = 24V, R _L = 0.1Ω, T _j = 25°C	—	—	1.5	V
I _{GT}	Gate trigger current		—	—	4000	mA
R _{th(j-f)}	Thermal resistance	Junction to fin	—	—	0.015	°C/W

PERFORMANCE CURVES


FG3300AH-50DA

HIGH POWER INVERTER USE
PRESS PACK TYPE


MAXIMUM ON-STATE POWER DISSIPATION
CHARACTERISTICS
(SINGLE-PHASE HALF WAVE)




ALLOWABLE FIN TEMPERATURE VS.
AVERAGE ON-STATE CURRENT
(SINGLE-PHASE HALF WAVE)




MAXIMUM ON-STATE POWER DISSIPATION
CHARACTERISTICS
(RECTANGULAR WAVE)




ALLOWABLE FIN TEMPERATURE VS.
AVERAGE ON-STATE CURRENT
(RECTANGULAR WAVE)



GATE TRIGGER CURRENT VS.
JUNCTION TEMPERATURE
(TYPICAL)



TURN ON TIME, TURN ON DELAY TIME
VS. TURN ON GATE CURRENT
(TYPICAL)



FG3300AH-50DA

HIGH POWER INVERTER USE
PRESS PACK TYPE

