






LOC		DIST		REVISIONS						
AD		47		P	LTR	DESCRIPTION	DATE	DWN	APVD	
					C	REVISED PER ECO-11-013132	13JUL2011	HMR	MH	

- 1 CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF
TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON
TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
- 2 PHOSPHOR BRONZE
- 3 GLASS FILLED POLYESTER
- 4 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 5 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 6 DRILLED HOLE DIAMETER 0.7±0.025
FINISHED HOLE DIA 0.60±0.05 REF
COPPER THICKNESS 0.025-0.050
TIN LEAD THICKNESS 0.004-0.010
- 7 CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995
- 8 HOLE DIAMETER:
2.4 FOR USE WITH P/N 532828, STATIC DISCHARGE, GUIDE PIN, HDI
3.4 FOR USE WITH P/N 120759, FEED THROUGH, GUIDE PIN
- 9 APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD



RECOMMENDED
PRINTED CIRCUIT BOARD
LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD

120684-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	H. MOLL	5-25-99	 TE Connectivity				
TOLERANCES UNLESS OTHERWISE SPECIFIED:				CHK	H. ANDREWS	5-25-99					
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	H. ANDREWS	5-25-99	NAME				
mm				PRODUCT SPEC			SHROUD ASSEMBLY, 6 ROW, 30 POSITION, LEFT HAND, Z-PACK HS3				
				APPLICATION SPEC							
9 PLG ±		±		WEIGHT			SIZE		CAGE CODE		
2 PLG ±0.13		±		CUSTOMER DRAWING			A1		00779		
5 PLG ±		±		SCALE			6:1		SHEET		
4 PLG ±		±		OF			1		REV		
ANGLES		±		C							
FINISH		GROUND CONTACT:		CONTACTS:		2		A1		00779	
MATERIAL:		HOUSING: 3		CONTACTS: 2		C=120684					