







1. ZINC DIECAST BODY AND HEAD WITH STEEL COVER. BODY AND COVER FINISHED IN MICRO SWITCH BLUE EPOXY PAINT. HEAD FINISHED IN BLACK EPOXY PAINT.
2. MINIMUM OPERATING VELOCITY (V_{min}) = 0.26 rad/s
MAXIMUM OPERATING VELOCITY (V_{max}) = 25 rad/s
MAXIMUM OPERATING FREQUENCY (F_{max}) = 250 OPS/MIN
3. FREE POSITION (FP), OPERATING POINT (OP), OVERTRAVEL (OT) AND PRETRAVEL (PT) ALL TO EN50047.
4. MAXIMUM TIGHTENING TORQUE FOR FIXING SCREW = 0.5Nm (4.4in.LB)
5. MAXIMUM TIGHTENING TORQUE FOR FIXING SCREW = 0.8Nm (7in.LB)

STANDARD SILVER CONTACTS		GOLD PLATED CONTACTS					
ELECTRICAL RATING		ELECTRICAL RATING		ENVIRONMENTAL			
AC		DC		IP66 NEMA 1, 4, 12, 13 TEMP RANGE : -25°C TO 85°C -13°F TO 185°F STORAGE : -40°C TO 85°C -40°F TO 185°F SHOCK : 50G PER IEC 68-2-27 VIBRATION : 10G PER IEC 68-2-6			
A300 Ue	AC15 Ie	Q300 Ue	DC13 Ie			  IEC 947-5-1 EN50047	
VOLTS	AMPS	VOLTS	AMPS				
120	6	125	0.55	IV 10μA MIN.			
240	3	250	0.27	50V 100mA MAX.			
THE COPYRIGHT OF THIS DRAWING IS THE PROPERTY OF HONEYWELL LTD. THE DRAWING IS SUPPLIED IN CONFIDENCE AND MUST NOT BE USED FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS SUPPLIED.				THIRD PROJECTION 	SCALE 1:1 DIMENSIONS ARE IN MM/INCHES.	MODIFY ON CAD SYSTEM ONLY	



BLANK = LEVER TO FRONT, SWITCHING IN BOTH DIRECTIONS.



NOTE:- CABLE AND CONNECTOR WILL BE FITTED TO BOTTOM EXIT CONDUIT ONLY. OTHER OPTIONS CUSTOMER SPECIAL 'N' LISTING.