

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [03-09-1064](#)
Status: **Active**
Overview: [Standard .093" Pin and Socket Connectors](#)
Description: 2.36mm Diameter Standard .093" Pin and Socket Receptacle Housing, 6 Circuits, Dual Row

Documents:
[3D Model](#) [Product Specification PS-43660-9999 \(PDF\)](#)
[Drawing \(PDF\)](#) [Packaging Specification PK-1261-001 \(PDF\)](#)
[Product Specification PS-02-09 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Crimp Housings
Series [1261](#)
Application Power, Wire-to-Wire
Comments 14.0A max. can be achieved when housing is used with 42477 or 42478 terminals
Overview [Standard .093" Pin and Socket Connectors](#)
Product Name Standard .093"
UPC 800753618589

Physical

Circuits (maximum) 6
Color - Resin Natural
Flammability 94V-2
Gender Receptacle
Glow-Wire Compliant No
Material - Resin Nylon
Net Weight 2.618/g
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 5.03mm
Stackable No
Temperature Range - Operating -40°C to +105°C

Electrical

Current - Maximum per Contact 11A

Material Info

Old Part Number 1261-R3

Reference - Drawing Numbers

Packaging Specification PK-1261-001
Product Specification PS-02-09, PS-43660-9999
Sales Drawing SD-1261-*




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[1261Series](#)

Mates With
[03-09-2061](#) , [03-09-2062](#) , [03-09-7062](#) , [3099](#)

Use With
[1189](#) Crimp Terminals, [1190](#) Crimp Terminals, [1376](#) Male PC Tail Terminals, [1377](#) Female PC Tail Terminals, [1380](#) Male Crimp Terminals, [1381](#) Female Crimp Terminals, [1433](#) Crimp Terminals, [1434](#) Male Crimp Terminals, [1973](#)