

### Typical Applications

The HMC224MS8 is ideal for:

- UNII & HiperLAN
- PCMCIA WirelessLAN

### Features


Low Cost 5-6 GHz Switch

Ultra Small Package: MSOP8

High Input P1dB: +33 dBm

Single Positive Supply: +3 to +8V

### Functional Diagram



### General Description


The HMC224MS8 is a low-cost SPDT switch in an 8-lead MSOP package for use in transmit-receive applications. The device can control signals from 5.0 to 6.0 GHz and is especially suited for 5.2 GHz UNII and 5.8 GHz ISM applications with only 1.2 dB loss. The design provides exceptional power handling performance; input P1dB = +33 dBm at 5 Volt bias. RF1 and RF2 are reflective shorts when "Off". On-chip circuitry allows single positive supply operation at very low DC current with control inputs compatible with CMOS and most TTL logic families. No DC blocking capacitors are required on RF I/O ports.

### Electrical Specifications, $T_A = +25^\circ\text{C}$ , $V_{dd} = +5\text{ Vdc}$ , 50 Ohm System


| Parameter                        | Frequency                        | Min.          | Typ. | Max. | Units |
|----------------------------------|----------------------------------|---------------|------|------|-------|
| Insertion Loss                   | 5.0 - 6.0 GHz                    |               | 1.3  | 1.6  | dB    |
|                                  | 5.1 - 5.4 GHz                    |               | 1.2  | 1.5  | dB    |
|                                  | 5.4 - 5.9 GHz                    |               | 1.3  | 1.6  | dB    |
| Isolation                        | 5.0 - 6.0 GHz                    | 20            | 24   |      | dB    |
|                                  | 5.1 - 5.4 GHz                    | 26            | 31   |      | dB    |
|                                  | 5.4 - 5.9 GHz                    | 22            | 27   |      | dB    |
| Return Loss                      | RF Common                        | 5.0 - 6.0 GHz | 11   | 15   | dB    |
|                                  |                                  | 5.1 - 5.9 GHz | 12   | 16   | dB    |
|                                  | RF1 & RF2                        | 5.0 - 6.0 GHz | 11   | 14   | dB    |
|                                  |                                  | 5.1 - 5.9 GHz | 11   | 15   | dB    |
| Input Power for 1 dB Compression | 0/3V Control                     | 5.0 - 6.0 GHz | 27   | 31   | dBm   |
|                                  | 0/5V Control                     | 5.0 - 6.0 GHz | 29   | 33   | dBm   |
| Input Third Order Intercept      | 0/3V Control                     | 5.0 - 6.0 GHz | 31   | 35   | dBm   |
|                                  | 0/5V Control                     | 5.0 - 6.0 GHz | 33   | 37   | dBm   |
| Switching Characteristics        | 5.0 - 6.0 GHz                    |               |      |      |       |
|                                  | tRISE, tFALL (10/90% RF)         |               | 10   |      | ns    |
|                                  | tON, tOFF (50% CTL to 10/90% RF) |               | 25   |      | ns    |

## GaAs MMIC T/R SWITCH 5.0 - 6.0 GHz


### Insertion Loss



### Isolation



### Return Loss



### Absolute Maximum Ratings

|                               |                 |
|-------------------------------|-----------------|
| Bias Voltage Range (Vdd)      | -0.2 to +12 Vdc |
| Control Voltage Range (A & B) | -0.2 to Vdd Vdc |
| Storage Temperature           | -65 to +150 °C  |
| Operating Temperature         | -40 to +85 °C   |

### Truth Table

\*Control Input Voltage Tolerances are  $\pm 0.2$  Vdc.




| Bias      | Control Input* |         | Bias Current | Control Current | Control Current | Signal Path State |           |
|-----------|----------------|---------|--------------|-----------------|-----------------|-------------------|-----------|
| Vdd (Vdc) | A (Vdc)        | B (Vdc) | Idd (uA)     | Ia (uA)         | Ib (uA)         | RF to RF1         | RF to RF2 |
| 3         | 0              | 0       | 10           | -5              | -5              | OFF               | OFF       |
| 3         | 0              | Vdd     | 10           | -10             | 0               | ON                | OFF       |
| 3         | Vdd            | 0       | 10           | 0               | -10             | OFF               | ON        |
| 5         | 0              | 0       | 45           | -22             | -23             | OFF               | OFF       |
| 5         | 0              | Vdd     | 45           | -5              | -40             | ON                | OFF       |
| 5         | Vdd            | 0       | 115          | -40             | -5              | OFF               | ON        |

Caution: Do not operate in 1dB compression at power levels above +33 dBm and do not "hot switch" power levels greater than +23 dBm (Vdd = +5Vdc).

DC blocks are not required at ports RFC, RF1 and RF2.

## GaAs MMIC T/R SWITCH 5.0 - 6.0 GHz


### Outline Drawing



#### NOTES:

1. PACKAGE BODY MATERIAL: LOW STRESS INJECTION MOLDED PLASTIC SILICA AND SILICON IMPREGNATED.
2. LEADFRAME MATERIAL: COPPER ALLOY
3. LEADFRAME PLATING: Sn/Pb SOLDER
4. DIMENSIONS ARE IN INCHES [MILLIMETERS].
5. DIMENSION DOES NOT INCLUDE MOLDFLASH OF 0.15mm PER SIDE.
6. DIMENSION DOES NOT INCLUDE MOLDFLASH OF 0.25mm PER SIDE.
7. ALL GROUND LEADS MUST BE SOLDERED TO PCB RF GROUND.


### Typical Application Circuit



#### Notes:

1. Control Inputs A and B can be driven directly with CMOS logic (HC) with V of 3 to 8 Volts applied to the CMOS logic gates and to pin 4 of the RF switch.
2. Set V to 5 Volts and use HCT series logic to provide a TTL driver interface.
3. Highest RF signal power capability is achieved with V set to +10V. However, the switch will operate properly (but at lower RF power capability) at bias voltages down to +3V.
4. RF ByPass: Do not use RF bypass capacitors on Vdd, A or B ports. Resistors R1, R2, R3 = 100 Ohms should be placed close to the Vdd, A and B ports. Use resistor size 0402 to minimize parasitic inductances and capacitances.
5. DC Blocking capacitors are not required for each RF port.
6. Evaluation PCB available.

### Evaluation PCB



### List of Material

| Item                                  | Description                      |
|---------------------------------------|----------------------------------|
| J1 - J3                               | PC Mount SMA RF Connector        |
| J4 - J7                               | DC Pin                           |
| R1, R3                                | 100 $\Omega$ resistor, 0402 Pkg. |
| U1                                    | HMC224MS8 T/R Switch             |
| PCB*                                  | 104518 Evaluation PCB            |
| * Circuit Board Material: Rogers 4350 |                                  |

The circuit board used in the final application should be generated with proper RF circuit design techniques. Signal lines at the RF port should have 50 ohm impedance and the package ground leads should be connected directly to the ground plane similar to that shown above. The evaluation circuit board shown above is available from Hittite Microwave Corporation upon request.