


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	P2	REVISED PER ECR-12-011660		25JAN13	KH	TM	

- 1 PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
- 2 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN LEAD ON SOLDER TAIL END.
- 3 CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 DRAIN HOLES LOCATED AS SHOWN. OPTIONAL CONSTRUCTION - ALL DRAIN HOLES LOCATED 90° AS SHOWN IN DETAIL A.
- 6 CONTACT IS PLATED OVERALL WITH 0.00127 [.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 7 SUPERSEDED BY 350826-4




3-DIMENSIONAL MODEL
NTS


6	PHOSPHOR BRONZE, GOLD	NYLON,UL94V-0,WHITE	350826-4
	PHOSPHOR BRONZE, GOLD	NYLON,UL94V-0,WHITE	350826-2
	PHOSPHOR BRONZE, PRE-TIN	NYLON,UL94V-0,WHITE	350826-1
	CONTACT MATERIAL AND FINISH	HOUSING MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS	10-02-98	TE Connectivity	
		CHK R. SWING	10-02-98		
DIMENSIONS: mm [INCHES]		APVD M. TRULL	10-02-98	NAME	
		PRODUCT SPEC		SOCKET HEADER ASSEMBLY, 4 CIRCUIT UNIVERSAL MATE-N-LOK™	
		APPLICATION SPEC		SIZE	CAGE CODE
				DRAWING NO	RESTRICTED TO
MATERIAL SEE TABLE		WEIGHT		A100779	350826
		CUSTOMER DRAWING		SCALE	SHEET
				5:1	1 OF 1
					REV P2

SEE DETAIL A



CONTACT
4 REQ'D




HOUSING

26.67
[1.050]


3

7.62
[.300]


0.25 MAX-
[.010]
CUT-OFF TAB



POINT OF MEASUREMENT



DETAIL A
OPTIONAL CONSTRUCTION



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 [.062] THICK P.C. BOARD