

**FDS6644**

## 30V N-Channel PowerTrench® MOSFET

## General Description



This N-Channel MOSFET has been designed specifically to improve the overall efficiency of DC/DC converters using either synchronous or conventional switching PWM controllers. It has been optimized for low gate charge, low  $R_{DS(ON)}$  and fast switching speed.

## Applications

- DC/DC converter

## Features

- 13 A, 30 V.  $R_{DS(ON)} = 8.5 \text{ m}\Omega$  @  $V_{GS} = 10 \text{ V}$   
 $R_{DS(ON)} = 10.5 \text{ m}\Omega$  @  $V_{GS} = 4.5 \text{ V}$
- High performance trench technology for extremely low  $R_{DS(ON)}$
- Low gate charge (25 nC typical)
- High power and current handling capability



## Absolute Maximum Ratings

$T_A=25^\circ\text{C}$  unless otherwise noted

Symbol	Parameter	Ratings	Units
$V_{DSS}$	Drain-Source Voltage	30	V
$V_{GSS}$	Gate-Source Voltage	$\pm 16$	V
$I_D$	Drain Current – Continuous – Pulsed	13	A
		52	
$P_D$	Power Dissipation for Single Operation	2.5	W
		1.4	
		1.2	
$T_J, T_{STG}$	Operating and Storage Junction Temperature Range	–55 to +175	°C

## Thermal Characteristics




Thermal Characteristics				
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	(Note 1a)	50	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	(Note 1c)	125	°C/W
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	(Note 1)	25	°C/W

## Package Marking and Ordering Information

Device Marking	Device	Reel Size	Tape width	Quantity
FDS6644	FDS6644	13"	12mm	2500 units

## Electrical Characteristics

$T_A = 25^\circ\text{C}$  unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
<b>Off Characteristics</b>						
$BV_{DSS}$	Drain–Source Breakdown Voltage	$V_{GS} = 0 \text{ V}$ , $I_D = 250 \mu\text{A}$	30			V
$\Delta BV_{DSS}$ $\Delta T_J$	Breakdown Voltage Temperature Coefficient	$I_D = 250 \mu\text{A}$ , Referenced to $25^\circ\text{C}$		27		$\text{mV/}^\circ\text{C}$
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS} = 24 \text{ V}$ , $V_{GS} = 0 \text{ V}$		1		$\mu\text{A}$
$I_{GSSF}$	Gate–Body Leakage, Forward	$V_{GS} = 16 \text{ V}$ , $V_{DS} = 0 \text{ V}$		100		nA
$I_{GSSR}$	Gate–Body Leakage, Reverse	$V_{GS} = -16 \text{ V}$ , $V_{DS} = 0 \text{ V}$		-100		nA
<b>On Characteristics</b> (Note 2)						
$V_{GS(\text{th})}$	Gate Threshold Voltage	$V_{DS} = V_{GS}$ , $I_D = 250 \mu\text{A}$	1	1.5	3	V
$\Delta V_{GS(\text{th})}$ $\Delta T_J$	Gate Threshold Voltage Temperature Coefficient	$I_D = 250 \mu\text{A}$ , Referenced to $25^\circ\text{C}$		-5		$\text{mV/}^\circ\text{C}$
$R_{DS(\text{on})}$	Static Drain–Source On–Resistance	$V_{GS} = 10 \text{ V}$ , $I_D = 13 \text{ A}$ $V_{GS} = 4.5 \text{ V}$ , $I_D = 11.8 \text{ A}$ $V_{GS} = 10 \text{ V}$ , $I_D = 13 \text{ A}$ , $T_J = 125^\circ\text{C}$		6.5 7.5 10	8.5 10.5 13	$\text{m}\Omega$
$I_{D(\text{on})}$	On–State Drain Current	$V_{GS} = 10 \text{ V}$ , $V_{DS} = 5 \text{ V}$	26			A
$g_{FS}$	Forward Transconductance	$V_{DS} = 5 \text{ V}$ , $I_D = 13 \text{ A}$		74		S
<b>Dynamic Characteristics</b>						
$C_{iss}$	Input Capacitance	$V_{DS} = 15 \text{ V}$ , $V_{GS} = 0 \text{ V}$ , $f = 1.0 \text{ MHz}$		3087		pF
$C_{oss}$	Output Capacitance			489		pF
$C_{rss}$	Reverse Transfer Capacitance			185		pF
<b>Switching Characteristics</b> (Note 2)						
$t_{d(\text{on})}$	Turn–On Delay Time	$V_{DD} = 15 \text{ V}$ , $I_D = 1 \text{ A}$ , $V_{GS} = 10 \text{ V}$ , $R_{\text{GEN}} = 6 \Omega$		10	20	ns
$t_r$	Turn–On Rise Time			12	22	ns
$t_{d(\text{off})}$	Turn–Off Delay Time			48	77	ns
$t_f$	Turn–Off Fall Time			10	20	ns
$Q_g$	Total Gate Charge	$V_{DS} = 15 \text{ V}$ , $I_D = 13 \text{ A}$ , $V_{GS} = 5 \text{ V}$		25	35	nC
$Q_{gs}$	Gate–Source Charge			7.5		nC
$Q_{gd}$	Gate–Drain Charge			6.5		nC
<b>Drain–Source Diode Characteristics and Maximum Ratings</b>						
$I_S$	Maximum Continuous Drain–Source Diode Forward Current			2.1		A
$V_{SD}$	Drain–Source Diode Forward Voltage	$V_{GS} = 0 \text{ V}$ , $I_S = 2.1 \text{ A}$ (Note 2)		0.7	1.2	V
<b>Notes:</b>						
1. $R_{\text{JJA}}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. $R_{\text{JJC}}$ is guaranteed by design while $R_{\text{JCA}}$ is determined by the user's board design.						
						
a) $50^\circ\text{C/W}$ when mounted on a $1\text{in}^2$ pad of 2 oz copper						
						
b) $105^\circ\text{C/W}$ when mounted on a $.04 \text{ in}^2$ pad of 2 oz copper						
						
c) $125^\circ\text{C/W}$ when mounted on a minimum pad.						
Scale 1 : 1 on letter size paper						
2. Pulse Test: Pulse Width < $300\mu\text{s}$ , Duty Cycle < 2.0%						

## Typical Characteristics




Figure 1. On-Region Characteristics.




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage.




Figure 3. On-Resistance Variation with Temperature.




Figure 4. On-Resistance Variation with Gate-to-Source Voltage.




Figure 5. Transfer Characteristics.




Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature.

## Typical Characteristics




Figure 7. Gate Charge Characteristics.




Figure 8. Capacitance Characteristics.




Figure 9. Maximum Safe Operating Area.




Figure 10. Single Pulse Maximum Power Dissipation.




Figure 11. Transient Thermal Response Curve.

Thermal characterization performed using the conditions described in Note 1c.  
Transient thermal response will change depending on the circuit board design.

## TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACE <sup>TM</sup>	FAST <sup>®</sup>	OPTOLOGIC <sup>TM</sup>	SMART START <sup>TM</sup>	VCX <sup>TM</sup>
Bottomless <sup>TM</sup>	FASTR <sup>TM</sup>	OPTOPLANAR <sup>TM</sup>	STAR*POWER <sup>TM</sup>	
CoolFET <sup>TM</sup>	FRFET <sup>TM</sup>	PACMAN <sup>TM</sup>	Stealth <sup>TM</sup>	
CROSSVOLT <sup>TM</sup>	GlobalOptoisolator <sup>TM</sup>	POP <sup>TM</sup>	SuperSOT <sup>TM</sup> -3	
DenseTrench <sup>TM</sup>	GTOT <sup>TM</sup>	Power247 <sup>TM</sup>	SuperSOT <sup>TM</sup> -6	
DOME <sup>TM</sup>	HiSeC <sup>TM</sup>	PowerTrench <sup>®</sup>	SuperSOT <sup>TM</sup> -8	
EcoSPARK <sup>TM</sup>	ISOPLANAR <sup>TM</sup>	QFET <sup>TM</sup>	SyncFET <sup>TM</sup>	
E <sup>2</sup> CMOS <sup>TM</sup>	LittleFET <sup>TM</sup>	QS <sup>TM</sup>	TinyLogic <sup>TM</sup>	
EnSigna <sup>TM</sup>	MicroFET <sup>TM</sup>	QT Optoelectronics <sup>TM</sup>	TruTranslation <sup>TM</sup>	
FACT <sup>TM</sup>	MicroPak <sup>TM</sup>	Quiet Series <sup>TM</sup>	UHC <sup>TM</sup>	
FACT Quiet Series <sup>TM</sup>	MICROWIRE <sup>TM</sup>	SILENT SWITCHER <sup>®</sup>	UltraFET <sup>®</sup>	

STAR\*POWER is used under license

## DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

## PRODUCT STATUS DEFINITIONS

### Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.