

Oscilloscope



Features:

- 4 Channels and EXT trigger, 60MHz Bandwidth
- 200MSPS real time sampling rate, 10k-16M Memory depth per channel
- Frequency Counter, FFT Spectrum Analysis
- 8-36V Wide range of input voltage, suitable for vehicle power
- More than 20 kinds of automatic measurement function, PASS/FAIL Check function, is suitable for engineering application

Specifications:

	Model	72-10177
Acquisition	Sample Mode	Real-Time Sample
	Sample Rate	200MSPS
	Average	N acquisitions, all channels simultaneously, N is selectable from 2, 4, 8, 16, 64, and 128
Input	Input Coupling	DC, AC, GND
	Input Impedance	Resistance: 1M Ω ; Capacitance: 25pF
	PP-80,PP-150,PP-200 Probe Attenuation	10X
	Support Current Measure	1X, 10X
	Maximum Input Voltage	400Vpk (DC + peak)
Horizontal	Scanning Speed Range(Sec/Div)	5ns/div ~ 1000s/div(1-2-5 sequences)
	Sample Rate and Delay Time Accuracy	± 50 ppm(any interval ≥ 1 ms)
	Wave form Interpolation	Step, Linear, Sin(x)/x
	Memory Depth(Sample Points)	10K ~ 16M for each channel; 16M: 5ns/div-1000s/div
	Analog Bandwidth	60MHz (-3dB)
	A/D converter	8 bit resolution
Vertical	Vertical Scale(Volt/div) Range	10mV ~ 5V/div @ x1 probe(1,2,5 sequence);
		100mV ~ 50V/div @ x10 probe
	Position Range	± 4 division
	Selectable Analog Bandwidth Limit(typical)	20MHz
	Lower Frequency Response(-3dB)	≤ 10 Hz(at input BNC)
	Rise Time at BNC(typical)	≤ 5.8 ns
	DC Gain Accuracy	$\pm 3\%$

Oscilloscope



Trigger	Trigger Source		CH1,CH2, CH3, CH4, EXT
	Trigger Mode		Auto, Normal and Single
	Trigger Type		Edge, Pulse, Video, Alternative
	Trigger Sensitivity		0.02 div increments
	Trigger Level Range		±4V
	Trigger Level Accuracy		±4 division
	Edge Trigger Slope		Rising, Falling
	Pulse Width Trigger		Trigger Condition: Trigger when <, >, =, or ≠; Positive pulse or Negative pulse Pulse Width Range: Selectable from 20ns to 10s
	Video Trigger Type (Signal Formats and Field Rates)		Supports NTSC, PAL and SECAM broadcast systems for any field or any line
	Alternative Trigger		CH1/CH2/CH3/CH4: Internal Trigger, Edge, Pulse Width, Video
Measurement	Cursor Measure		Amplitude difference between cursors (ΔV); Time difference between cursors (Δt); Reciprocal of Δt in Hertz ($1/\Delta t$) (Cross, Trace, Horizontal, Vertical)
	Auto Measure	Voltage	Vp-p, Vmax, Vmin, Vmean, Vamp, Vtop, Vbase, Vmid, Vrms, Vcrms, Preshoot, Overshoot
		Time	Frequency, Period, Rise Time(10%~90%), Fall Time(10%~90%), Positive Width, Negative Width, Duty Cycle
Arbitrary Waveform Generator	Waveform Frequency		DC ~ 25MHz
	DAC clock		2K ~ 200MHz adjustable
	Frequency Resolution		0.10%
	Waveform Depth		4K Sample
	Vertical Resolution		12 bit
	Frequency Stability		<30ppm
	Wave Amplitude		±3.5V Max.
	Output Impedance		50Ω
	Output Current		50mA ,Ipeak=50mA
	System BW		25MHz
	Harmonic Distortion		-50dB(1KHz), -40dB(10KHz)
Environmental	Temperature		Operating: 0°C to 40°C Non-operating: -20°C to +60°C)
	Cooling Method		Forced air
	Humidity		Below +35°C, ≤90% relative humidity; +35°C to +40°C, ≤60% relative humidity
	Altitude		Operating: 3,000m or below; Non-operating: 15,000m or below

Oscilloscope



Mechanical	Size	190mm(L)×100mm(W)×35mm(H)
	Heavy	Without Packaged 0.29kg; Packaged 0.9kg;
Accessories	Probe	X1, X10 two passive probes. The passive probes have a 6MHz bandwidth (rated 100Vrms CAT III) when the switch is in the X1 position, and a maximum bandwidth (rated 300Vrms CAT II) when the switch is in the X10 position. Each probe consists of all necessary fittings.
	Adapter	A power adapter special for this product. In addition to the power adapter shipped with your instrument, you may purchase another one certified for the country of use.
	USB Line	A USB A-B line, used to connect external devices with USB-B interface like a printer or to establish communications between PC and the oscilloscope.
	Installation CD	A software installation CD and it also contains the user manual for the Tenma Oscilloscope.

Part Number Table

Description	Part Number
Oscilloscope, PC, 4 CH, 60MHz, AFG	72-10177

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

