

13

12

11

10

9

8

7

6

5

4

3

2

1

J

I

H

G

F





E

D

C

B

A



NOTES:


1. PART DESIGNED IN METRIC.
2. TERMINAL FOR USE WITH 5557 SERIES HOUSINGS.
3. MATES WITH 5558, 5566 AND 5569 SERIES CONNECTORS.
4. REFER TO DWG. NO. CS-5556*/5558* FOR CRIMP SPECIFICATIONS.
5. PRODUCT SPECIFICATION AND PROCESSING PARAMETERS SEE: PS-5556-001, PS-5556-002, PS-5556-003

MATERIAL:

- A. CDA 260 BRASS, .0080±.0004/(0.203±0.010) THICK.
- B. CDA 510 PHOS. BRONZE .0080±.0004/(0.203±0.010) THICK.

PLATING:

- A. SELECTIVE GOLD PLATE .000030/(0.00076) MIN., AND SELECTIVE MATTE TIN .000100/(0.00254) OVER .000050/(0.00127) NICKEL OVERALL.
- B. SELECTIVE GOLD PLATE .000015/(0.00038) MIN., AND SELECTIVE MATTE TIN .000100/(0.00254) OVER .000050/(0.00127) NICKEL OVERALL.
- C. SELECTIVE GOLD PLATE .000050/(0.00127) MIN., AND SELECTIVE MATTE TIN .000100/(0.00254) OVER .000050/(0.00127) NICKEL OVERALL.



REMOVED 28-30 GAGE EC NO: DRAWN/DUNE CHKD: APPR: A3	DESCRIPTION	QUALITY SYMBOLS ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
			mm	INCH	DRAWN BY CLS	DATE 08/16/04	TITLE TERMINAL MINI-FIT JR. FEMALE,CRIMP,SELECT GOLD BLANK-PLATE-FORM					
			4 PLACES ± --- ± ---	3 PLACES ± --- ± .010	CHECKED BY	DATE						
			2 PLACES ± 0.25 ± .014	1 PLACE ± 0.36 ± ---	GEP	DATE 08/16/04	MOLEX MOLEX INCORPORATED					
			ANGULAR ±1/2°		APPROVED BY YM	DATE 08/16/04						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE SHEET 2		DOCUMENT NO. SD-5556-900		SHEET NO. 1 OF 2			
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

12

11

10

9

8

7

6

5

4

3

2

1

