

PLL CLOCK MULTIPLIER

IDT5V80013


Description

The IDT5V80013 is the most cost effective way to generate a high-quality, high-frequency clock output. Using Phase-Locked Loop (PLL) techniques, the device employs IDT's proprietary MEMs oscillator technology to produce common output frequencies for consumer, computing, and embedded applications.


Features

- Packaged in a small form factor 16-pin QFN
- Eliminates the need for an external crystal or input clock source
- Max. ± 50 ppm error on CLK output
- Typical ± 75 ps short term cycle-cycle jitter
- Output voltage of 3.3V
- Operating voltage of 1.8V
- Supports industrial temperature range
- Supports output frequency on CLK up to 220MHz
- Advanced, low-power CMOS process

Block Diagram



Pin Assignment



CLK Output Frequency/Part Number Table

Frequency	Orderable Part Number
11.2896 MHz	5V80013-112NLGI
12 MHz	5V80013-012NLGI
12.288 MHz	5V80013-122NLGI
14.31818 MHz	5V80013-143NLGI
19.2 MHz	5V80013-192NLGI
20 MHz	5V80013-020NLGI
22.5792 MHz	5V80013-225NLGI
24 MHz	5V80013-024NLGI
24.576 MHz	5V80013-245NLGI
25 MHz	5V80013-025NLGI
26 MHz	5V80013-026NLGI
27 MHz	5V80013-027NLGI
33.3333 MHz	5V80013-333NLGI
33.8688 MHz	5V80013-338NLGI
38.864 MHz	5V80013-388NLGI
48 MHz	5V80013-048NLGI
50 MHz	5V80013-050NLGI
61.44MHz	5V80013-614NLGI
66.6666 MHz	5V80013-666NLGI
74.25 MHz	5V80013-742NLGI
74.175824 MHz	5V80013-741NLGI
125 MHz	5V80013-125NLGI

Note: Contact IDT for any other frequencies.

Pin Descriptions

Pin Number	Pin Name	Pin Type	Pin Description
1	VDD	Power	Connect to +1.8V.
2	GND	Ground	Connect this pin to ground.
3	GND	Ground	Connect this pin to ground.
4	OE	Input	Output enable pin for CLK output.
5	VDDO	Power	Connect to +3.3V.
6	VDD	Power	Connect to +1.8V.
7	VDD	Power	Connect to +1.8V.
8	GND	Ground	Connect this pin to ground.
9	CLK	Output	Single-ended clock output.
10	GND	Ground	Connect this pin to ground.
11	NC	–	No connect. Do not connect this pin to anything.
12	VDD	Power	Connect to +1.8V.
13	VDD	Power	Connect to +1.8V.
14	CAP-IN	–	This pin should be connectd to GND (pin 15) through a 10μF capacitor.
15	GND	Ground	Connect this pin to ground.
16	VDD	Power	Connect to +1.8V.

External Components

Decoupling Capacitor

As with any high-performance mixed-signal IC, the IDT5V80013 must be isolated from system power supply noise to perform optimally.

A decoupling capacitor of 0.01 μ F must be connected between VDD and GND. It must be connected close to the IDT5V80013 to minimize lead inductance. No external power supply filtering is required for the IDT5V80013.

Series Termination Resistor

A 33 Ω terminating resistor can be used next to the CLK pin. The total on-chip capacitance is approximately 12 pF.

Absolute Maximum Ratings

Stresses above the ratings listed below can cause permanent damage to the IDT5V80013. These ratings, which are standard values for IDT commercially rated parts, are stress ratings only. Functional operation of the device at these or any other conditions above those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods can affect product reliability. Electrical parameters are guaranteed only over the recommended operating temperature range.

Item	Rating
Supply Voltage, VDD	5 V
All Inputs and Outputs	-0.5 V to VDD+0.5 V
Ambient Operating Temperature (industrial temperature)	-40 to +85° C
Storage Temperature	-65 to +150° C
Soldering Temperature	260° C

Recommended Operation Conditions

Parameter	Min.	Typ.	Max.	Units
Ambient Operating Temperature (commercial)	0	–	+70	° C
Ambient Operating Temperature (industrial)	-40	–	+85	° C
Power Supply Voltage (measured in respect to GND)	+1.71	+1.8	+1.89	V

DC Electrical Characteristics

VDD=1.8 V $\pm$ 5% , VDDO = 3.3 V, Ambient temperature -40 to +85° C, unless stated otherwise

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Operating Voltage	VDD		1.71	1.8	1.89	V
Output Voltage	VDDO		3.135	3.3	3.465	V
Output High Voltage*	V _{OH}	I _{OH} = -2 mA	VDD-0.45			V
Output Low Voltage*	V _{OL}	I _{OL} = 2 mA			0.4	V
IDD Operating Supply Current		No load		15	22	mA
Input Capacitance				4		pF

*Note: Guaranteed by design.

AC Electrical Characteristics


VDD=1.8 V $\pm$ 5%, VDDO = 3.3 V, Ambient Temperature -40 to +85° C, unless stated otherwise

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Units
Output Frequency			See Page 2			MHz
Frequency Synthesis Error			-50		50	ppm
Output Clock Rise Time	t _{OR}	0.8 to 2.0 V		1		ns
Output Clock Fall Time	t _{OF}	2.0 to 0.8 V		1		ns
Output Clock Duty Cycle	t _{OD}	VDD/2	45	50	55	%
Short Term Cycle-to-Cycle Jitter	t _{ja}	CLK output		75	100	ps
One Sigma Clock Period Jitter	t _{js}	CLK output		15		ps
Long Term Jitter		CLK output			TBD	ps
Aging		First year			5	ppm
Power-up Time				10	45	ms

Note: Measured with a 7pF load.

Package Outline and Package Dimensions (16-pin QFN)

Package dimensions are kept current with JEDEC Publication No. 95



Millimeters		
Symbol	Min	Max
A	0.80	1.00
A1	0	0.05
A3	0.20 Reference	
b	0.18	0.30
e	0.50 BASIC	
N	16	
N _D	4	
N _E	4	
D x E BASIC	3.00 x 3.00	
D2	1.55	1.80
E2	1.55	1.80
L	0.30	0.50

Ordering Information

Part / Order Number	Marking	Shipping Packaging	Package	Temperature
5V80013-XXXNLG	TBD	Tubes	16-pin QFN	0 to +70° C
5V80013-XXXNLG8		Tape and Reel	16-pin QFN	0 to +70° C
5V80013-XXXNLGI		Tubes	16-pin QFN	-40 to +85° C
5V80013-XXXNLGI8		Tape and Reel	16-pin QFN	-40 to +85° C

See table on page 2 for specific -XXX orderable part numbers.

“G” after the two-letter package code are the Pb-free configuration and are RoHS compliant.

While the information presented herein has been checked for both accuracy and reliability, Integrated Device Technology (IDT) assumes no responsibility for either its use or for the infringement of any patents or other rights of third parties, which would result from its use. No other circuits, patents, or licenses are implied. This product is intended for use in normal commercial applications. Any other applications such as those requiring extended temperature range, high reliability, or other extraordinary environmental requirements are not recommended without additional processing by IDT. IDT reserves the right to change any circuitry or specifications without notice. IDT does not authorize or warrant any IDT product for use in life support devices or critical medical instruments.

Revision History

Rev.	Originator	Date	Description of Change
E	K.B.	06/10/10	1. Changed pin 1 to VDD; updated pinout and description table. 2. Changed pin 14 to CAP-IN; updated pinout and description table. 3. Deleted sentence on pg. 4: "A parallel resonant, fundamental mode crystal should be used."
G	J.C.	01/31/12	Added "Output voltage of 3.3V" bullet to Features
H	J.C.	02/03/12	1. Updated Features bullets 2. Updated IDD Operating Supply Current Typ. and Max. values 3. Updated Short Term C-C Jitter Typ. and Max. values
J	J.C.	02/23/12	Update "CLK Output Frequency/Part Number Tree" table by removing erroneous/invalid part numbers and updating frequencies

Innovate with IDT and accelerate your future networks. Contact:

www.IDT.com

For Sales

800-345-7015
408-284-8200
Fax: 408-284-2775

For Tech Support

www.idt.com/go/clockhelp

Corporate Headquarters

Integrated Device Technology, Inc.
www.idt.com

