


DO NOT SCALE

DIMENSIONS IN mm

METRIC

THIRD ANGLE

PROJECTION



NOTES:



INDICATION OF FIRST POSITION.






SNAP-IN POLARIZERS PN. 927636-2 OR 927637-2 CAN BE APPLIED HERE.




THERE IS NO CENTER STAND-OFF IN 10-26 POS. HEADERS.



THERE IS NO WINDOW FOR SNAP-IN POLARIZERS AT THIS END IN 10 AND 14 POS. HEADERS.



RECOMMENDED PCB-HOLE PATTERN



④ BOARD LOCK FOR AMP-LATCH PIN HEADER	BRONZE	5-10µm TIN OVER
③ PIN-CONTACT	BRASS	MATING SIDE: 0,8µm AU OR 0,8µm AMP DURAGOLD®/ OVER 1,27µm NI SOLDER SIDE: MIN. 3,0µm SN OVER 1,27µm NI
② LATCH	GLASSFILLED POLYESTER	GREY
① HOUSING	GLASSFILLED POLYESTER	GREY

100,6	90,4	96,5	86,4	78,7	64	6-216868-4
95,5	85,3	91,4	81,3	73,7	60	6-216868-0
82,8	72,6	78,7	68,6	61,0	50	5-216868-0
70,1	59,9	66,0	55,9	48,3	40	4-216868-0
62,5	52,3	58,4	48,3	40,6	34	3-216868-4
52,3	42,2	48,3	38,1	30,5	26	2-216868-6
44,7	34,5	40,6	30,5	22,9	20	2-216868-0
39,6	29,5	35,6	25,4	17,8	16	1-216868-6
37,1	26,9	33,0	22,9	15,2	14	1-216868-4
32,0	21,8	27,9	17,8	10,2	10	1-216868-0
DIM. "E"	DIM. "D"	DIM. "C"	DIM. "B"	DIM. "A"	NR. OF POSITIONS	PARTNUMBER
VARIABLE CONNECTOR DIMENSIONS						

COMPONENT NAME MATERIAL PLATING / COLOUR

CUSTOMER DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED
© COPYRIGHT 19- BY AMP HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.

THIS DRAWING IS UNPUBLISHED
RELEASED FOR PUBLICATION - , 19 -

AMP HOLLAND B.V.
's-Hertogenbosch,
The Netherlands.

NAME
AMP-LATCH EJECTION-STYLE PIN HEADER 90°

VERSION WITH LATCHES AND BOARD LOCK DEVICE

DR. : R.HOGEVEEN	CHK. : R.VERSTIJNEN	APP. : L.V. SOEST	DWG.No.	LOC.	SHEET	REV.LTR.
DATE: 10-01-90	DATE: 11-01-90	DATE: 22-01-90	C-216868	AI A3	1 OF 1	B1