



REV.	DATE	DESCRIPTION
NC	06/06/04	INITIAL RELEASE



NOTE:

1. CONTACT PIN TO SOLDER

Amphenol Connex									
Part Description N R/A CLAMP PLUG (FOR RG58C/U, 58/U, 142A/U, 223/U)									
Part No. 172316									
DWG. NO. 172316.DWG									
REV. NC SIZE A SCALE NA									
CAD FILE C:/172/172316.DWG									
APPROVALS DATE		06/06/04							
DRAWN G.R.S.		06/06/04							
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED, TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"									
DO NOT SCALE DRAWING									
QTY									
FINISH									
MATERIAL									
DESCRIPTION									
1 SHELL/BODY		BRASS							
2 INSULATOR		TEFLON							
3 CONTACT PIN		BRASS							
4 WASHER		BRASS							
5 GASKET		SILICONE							
6 END CAP / HEX NUT		BRASS							
7 NUT		BRASS							
8		NEXCOTE							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[172316](#)