

10 cm Breitbandlautsprecher / 4" Fullrange Speakers

FR 10 Art. No. 2020 – 4 Ω Art. No. 2021 – 8 Ω



10 cm (4") Breitbandlautsprecher mit guten Tieftoneigenschaften, ausgeglichenem Frequenzgang und hohem Wirkungsgrad. Besonders geeignet als Einbaulautsprecher für die Musikwiedergabe sowie zur Bestückung von ELA-Zeilen. **Zubehör:** Schutzgitter (Art. No. 4642, 4640, 4670, 4744)

Anwendungsmöglichkeiten: ELA-Zeilen, Deckenlautsprecher in Schienenfahrzeugen und Bussen, Car-HiFi Einbaulautsprecher, Elektronische Musikinstrumente

10 cm (4") fullrange speaker with good bass reproduction, balanced frequency response and high efficiency. Especially suitable as built-in speaker for music reproduction and as driver for 100 V network column speakers. **Accessories:** Protective grille (Art. No. 4642, 4640, 4670, 4744)




Typical applications: Network column speakers, Ceiling-mounted speakers in railway carriages and busses, Built-in car hi-fi speakers, Electronic musical instruments



Art. No. 4642 *) Art. No. 4744 *)



Art. No. 4640 *) Art. No. 4670 *)



FR 10 HMP Art. No. 4880 – 4 Ω




10 cm (4") Breitbandlautsprecher mit Polypropylenmembran, Hochtonkegel und Euro-Normkorb. Einfache Montage in Fahrzeugen mit Einbauorten für 10-cm-Lautsprecher.

Zubehör: Schutzgitter (Art.-No. 4642, 4640, 4744)

10 cm (4") full-range speaker with polypropylene diaphragm, dual cone and European standard basket. Simple fitting in vehicles with cut-outs for 10 cm speakers.

Accessories: Protective grille (Art.-No. 4642, 4640, 4744)






Art. No. 4642 *)



Art. No. 4640 *)



Art. No. 4744 *)



		FR 10	FR 10 HMP
Nenn-/Musikbelastbarkeit	Rated/maximum power	30 W / 50 W	20 W/30 W
Impedanz	Impedance	4 Ω/8 Ω	4 Ω
Übertragungsbereich (–10 dB)	Frequency response (–10 dB)	80–20000 Hz	90–20000 Hz
Mittlerer Schalldruckpegel	Mean sound pressure level	86 dB (1 W/1 m)	86 dB (1 W/1 m)
Grenzauslenkung x _{mech}	Excursion limit x _{mech}	± 4 mm	4 mm
Resonanzfrequenz	Resonance frequency	92 Hz/88 Hz	120 Hz
Obere Polplattenhöhe	Height of front pole-plate	3 mm	2 mm
Schwingspulendurchmesser	Voice coil diameter	20 mm Ø	14 mm Ø
Wickelhöhe	Height of winding	6 mm	5 mm
Schallwandöffnung	Cutout diameter	100 mm Ø	94 mm Ø
Gewicht netto	Net weight	0,38 kg	0,268 kg

Weitere Daten Seiten 184–185 / for further data see pages 184–185
*) Details und Zeichnungen siehe Seite 175–179 / Details and drawings see page 175–179

VISATON Lieferprogramm / Main Catalogue 2011/2012