







Copyright FCI.

D

C

B

A




TIN LEAD PART NUMBER

PART NUMBER	
200 Mating	D50P91C4GL00
500 Mating	D50P91C6GL00

LEAD FREE PART NUMBER

PART NUMBER	
200 Mating	D50P91C4GL00LF
500 Mating	D50P91C6GL00LF

PC board drilling dimensions
(after plating – thickness: 1.60 to 3.20 mm)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

European Views

www.fciconnect.com			surface ISO 1302 		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	PESSON	1995/10/03	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	1995/10/03			0.XX	±0.1				
Chr	LEGARE	1995/10/03	0.XX ±2		0.XXX	±0.1	ECN	I11-0062		
Appr	LEGARE	1995/10/03	Product family			D-SUB	Spec ref -			
			title MALE CONNECTOR DELTA D 50-EUROPE straight press fit				dwg no C01-8646-0377		Rev. F	
catalog no			-			CUSTOMER		sheet 1 of 1		

rev	ecn no	dr	date
B	-	LEN	1996/07/25
C	LS05-004	MPE	2005/02/10
D	LS06-0095	LGO	2006/06/28
E	LS06-0140	LGO	2006/09/25
F	I11-0062	RPK	2011/05/13
-	-	-	-
-	-	-	-

REV F - 2006-04-17

1

2

3

4

PDM: Rev:F

STATUS: Released

Printed: Oct 11, 2011