








NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. RATING: UL: 5A @ 250VAC; 8A @ 125VAC
5. INSULATION RESISTANCE: 50 MEGA-OHMS (INITIAL)
- ▲ 6. ELECTRICAL LIFE: 30,000 MAKE-AND-BREAK CYCLES min.
7. CONTACT MATERIAL: SILVER
8. PANEL THICKNESS RANGE: 0.50 - 5.00 mm
9. OPERATING TEMP.: -25°C to 55°C
10. STORAGE TEMP.: -40°C to 70°C
11. ▲ DENOTES CRITICAL PARAMETER.
12. 2002/95/EC (ROHS) COMPLIANT
13. PACKAGING: SHIPPED SEPARATELY IN BULK
14. LAMP: 28VAC INCANDESCENT
15. DEGREE OF PROTECTION: IP65



ISOMETRIC

MDP16OAR33R
(F083111)SOCKET PROTECTOR
REMOVED (FOR
CLARIFICATION)

E-SWITCH®



TITLE MDP16OAR3103R

SCALE 1.25 : 1

DATE 2/11/2010

DR BLR

DWG XF0812P

REV A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

A	18776	RELEASED FOR PRODUCTION	2/11/10	BLR
REV	PCR NO	DESCRIPTION	DATE	BY