

9302 Multi-Conductor - Audio, Control and Instrumentation Cable

**Description:**

22 AWG solid tinned copper conductors, PVC insulation, twisted pairs, overall Beldfoil shield (100% coverage), 22 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
2	22	Solid	TC - Tinned Copper

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.013

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
22	7x30		TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.032

Overall Cabling

Overall Nominal Diameter: 0.244 in.

Pair**Pair Color Code Chart:**

Number	Color
1	Black & Red
2	Black & White

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	80°C (UL AWM Style 2464)
Bulk Cable Weight:	27.300 lbs/1000 ft.
Max. Recommended Pulling Tension:	31 lbs.
Min. Bend Radius (Install)/Minor Axis:	2.500 in.

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: CMG

9302 Multi-Conductor - Audio, Control and Instrumentation Cable

CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 80°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

C(UL) Flame Test:	FT4
-------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)**Nom. Inductance:**

Inductance (μH/ft)
0.2

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
50

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)
35

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
16.5

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
10.5

Max. Operating Voltage - UL:

Voltage
300 V RMS (UL AWM Style 2464)

Max. Recommended Current:

Current
2.35 Amps per conductor @ 25°C

Put Ups and Colors:


Item #	Putup	Ship Weight	Color	Notes	Item Desc
9302 060U1000	1,000 FT	29.000 LB	CHROME		2 PR #22 PVC FS PVC
9302 060U500	500 FT	15.500 LB	CHROME		2 PR #22 PVC FS PVC
9302 0601000	1,000 FT	31.000 LB	CHROME	C	2 PR #22 PVC FS PVC
9302 060500	500 FT	15.000 LB	CHROME	C	2 PR #22 PVC FS PVC

Notes:

C = CRATE REEL PUT-UP.

Overall Beldfoil® Shield

Audio, Control and Instrumentation Cables

Description	Part No.	UL NEC/ C(UL) CEC Type	No. of Pairs	Color Code	Standard Lengths		Standard Unit Weight		Insulation Thickness		Jacket Thickness		Nominal OD		Nominal Capacitance			
					Ft.	m	Lbs.	kg	Inch	mm	Inch	mm	Inch	mm	* pF/ Ft.	* pF/ m	** pF/ Ft.	** pF/ m
22 AWG Solid Tinned Copper Conductors • Twisted Pairs • Overall Beldfoil Shield (100% Coverage) • 22 AWG Stranded TC Drain Wire																		
PVC Insulation • Chrome PVC Jacket																		
 Shorting Fold	UL AWM Style 2464 (300V 80°C)	9302	NEC: CMG CEC: CMG FT4	2	See Chart 3 (Tech Info Section)	U-500 500 U-1000 1000	U-152.4 152.4 U-304.8 304.8	15.5 15.0 29.0 31.0	7.0 6.8 13.2 14.1	.013 .33	.032 .81	.244 6.20	35 115	50 164				
		9305	NEC: CMG CEC: CMG FT4	4	See Chart 3 (Tech Info Section)	100 U-500 500 U-1000 1000	30.5 U-152.4 152.4 U-304.8 304.8	4.9 22.0 22.5 43.0 45.0	2.2 10.0 10.2 19.5 20.4	.013 .33	.032 .81	.265 6.73	35 115	50 164				
		9306	NEC: CMG CEC: CMG FT4	6	See Chart 3 (Tech Info Section)	500 1000	152.4 304.8	31.5 62.0	14.3 28.2	.013 .33	.032 .81	.315 8.00	35 115	50 164				
		9309	NEC: CMG CEC: CMG FT4	9	See Chart 3 (Tech Info Section)	500 1000	152.4 304.8	44.5 86.0	20.2 39.1	.013 .33	.033 .84	.363 9.22	35 115	50 164				
		9315	NEC: CMG CEC: CMG FT4	15	See Chart 3 (Tech Info Section)	500 1000	152.4 304.8	67.0 133.0	30.5 60.5	.013 .33	.037 .94	.449 11.41	35 115	50 164				
		9319	NEC: CMG CEC: CMG FT4	19	See Chart 3 (Tech Info Section)	500 1000	152.4 304.8	85.0 165.0	38.6 75.0	.013 .33	.040 1.02	.495 12.57	35 115	50 164				
		9327	NEC: CMG CEC: CMG FT4	27	See Chart 3 (Tech Info Section)	500 1000	152.4 304.8	116.0 230.0	52.7 104.5	.013 .33	.045 1.14	.615 15.62	35 115	50 164				
		300V RMS, 60°C	8751	NEC: CMG CEC: CMG FT4	51	Request Technical Bulletin T/8-4	1000†	304.8	384.0	174.5	.010	.25	.050	1.27	.710	18.03	30	98
For 38-pair polypropylene version of 8751, see 8752.																		

For 38-pair polypropylene version of 8751, see 8752.

Description	Part No.	UL NEC/ C(UL) CEC Type	No. of Pairs	Color Code	Standard Lengths		Standard Unit Weight		Nom. DCR		Nominal OD		Nom. Imp. (Ω)	Nom. Vel. of Prop.	Nom. Capacitance			
					Ft.	m	Lbs.	kg	Cond.	Shield	Inch	mm			* pF/Ft.	* pF/m	** pF/Ft.	** pF/m
22 AWG Solid Tinned Copper Conductors • Twisted Pairs • Duofoil® Shield (100% Coverage) • 22 AWG Stranded Tinned Copper Drain Wire																		
Datalene® Insulation • Black PVC Jacket																		
UL AWM Style 2668 (300V 60°C)	9184	NEC: CM	2	Black & Yellow,	500	152.4	29.0	13.2	16.5Ω/M'	8.0Ω/M'	.385	9.78	150	78%	8.7	28.5	14.1	46.3
		CEC: CM		Red & Blue	1000	304.8	59.0	26.8	54.13Ω/km	26.2Ω/km								



DCR = DC Resistance • TC = Tinned Copper

*Capacitance between conductors.

**Capacitance between one conductor and other conductors connected to shield.

† Spools are one piece, but length may vary -0 to +20% from length shown.

Datalene insulation features include low dielectric constant and a dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.