



PART NO.	ENG. NO.	
02-06-1101	1561-(P901)	
02-06-1103	1561-(P901)L	
02-06-5101	1561-(P561)	
02-06-5102	1561-(P561)L	
02-06-5108	1561-(P228)	
02-06-5109	1561-(P228)L	
02-06-5100	1561-(P550)	
02-06-5103	1561-(P550)L	
02-06-5105	1561-(P591)	
02-06-5104	1561-(P591)L	
02-06-1118	1561-1(P901)	
NOT TOOLED	1561-1(P901)L	



SECT. "B-B"
SCALE:10X

SECT. "C-C"
SCALE:10X

LEGEND


1561-*(****)*

BLANK=WITH LOCKING TABS
1=WITHOUT LOCKING TABS


P=PREPLATE
BLANK=POSTPLATE

FORM
BLANK=CHAIN
L=LOOSE

FINISH CODE




(.25)
MAX.
.010
CARRIER CUTOFF




(.25)
MAX.
.010
CARRIER CUTOFF

(1.50/1.42)
DIA.
.059/.056



SELECT GOLD
PLATE DEPTH
(WHEN SPECIFIED)



CARRIER VIEW
ACTUAL SIZE

(2.03)
.080

(1.52)
.060
(.38)
.015

SECT. "A-A"

NOTES:

- MATERIAL: BRASS
- FINISH:
 - HOT TIN DIP (.00051)/.000020 MIN.
 - SELECT GOLD PLATE (.00075)/.000030 MIN. IN CONTACT AREA, SELECT TIN, (.00250)/.000100 MIN. IN CRIMP AREA OVER (.00125)/.000050 MIN. NICKEL OVERALL.
 - SELECT GOLD PLATE (.00076)/.000030 MIN. IN CONTACT AREA, OVER (.00127)/.000050 MIN. NICKEL OVERALL.
 - SELECT GOLD PLATE (.00175)/.000050 MIN. IN CONTACT AREA, OVER (.00127)/.000050 MIN. NICKEL OVERALL WITH (.000025)/.000010 MAX. GOLD FLASH OVERALL.
 - SELECT GOLD PLATE (.00038)/.000015 MIN. IN CONTACT AREA, OVER (.00076)/.000030 MIN. NICKEL OVERALL WITH (.000025)/.000010 MAX. GOLD FLASH OVERALL.
- PRODUCT SPECIFICATION: PS-02-06.
- PACKAGING INFORMATION: NOT AVAILABLE
- TERMINAL FOR USE WITH (1.57)/.062 DIA. SERIES HOUSINGS AND WILL ACCEPT 18 THRU 24 AWG WIRE WITH (1.52/3.05)/.060/.120 INSULATION DIA.
- PARTS CONFORM TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

CORRECT TOLERANCE	REV	DESCRIPTION	QUALITY SYMBOLS
EC NO: UCP2015-0937	AP1	2014/09/02 DRWN:KIPPER CHKD:NGUYEN APPR:FSMITH	

QUALITY SYMBOLS

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .010
2 PLACES	± 0.25	± .014
1 PLACE	± 0.36	± ---
0 PLACE	±	±
ANGULAR ±1/2°		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE	SCALE	DESIGN UNITS
MM/IN	6:1	INCH
DRAWN BY	DATE	TITLE
GEW	1991/02/19	CRIMP TERMINAL, FEMALE .062 DIA. FOR 18-24 AWG WIRE
CHECKED BY	DATE	
RW	1991/02/19	
APPROVED BY	DATE	
GW	1991/02/19	
MATERIAL NO.	DOCUMENT NO.	SHEET NO.
SEE CHART	SD-1561-*	1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION