

Static Desiccator Dehydrator with UV Filter



- To meet our global customer's RoHS environmental needs, we have changed our desiccant to a cobalt-chloride free desiccant. The compliant desiccant is orange when dry and turns green when saturated.

Product Classification

Product Type	Dehydrator
---------------------	------------

General Specifications


Dehydrator Type	Desiccant
Desiccant Capacity	283 liters (10 cu ft) at 80% RH, +20 °C
Mounting	Pole
Port Count	1
Port Type	3/8 in PE tube x 1/8 NPT

Dimensions

Product Height	127 mm 5 in
Product Width	50.8 mm 2 in
Product Depth	50.8 mm 2 in
Volume Capacity, maximum	0.028 m ³ 0.999 ft ³
Volume Capacity, minimum	0 m ³ 0 ft ³

SD-003UV

Outline Drawing-Front



SD-003UV Front View

Environmental Specifications

Operating Temperature -29 °C to +49 °C (-20 °F to +120 °F)

Packaging and Weights

Height, packed	86 mm 3.386 in
Width, packed	165.1 mm 6.5 in
Depth, packed	121.9 mm 4.799 in
Weight, gross	0.9 kg 1.984 lb
Weight, net	0.2 kg 0.441 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

