


| REVISIONS |                           |          |          |
|-----------|---------------------------|----------|----------|
| LTR       | DESCRIPTION               | DATE     | APPROVED |
| J         | REVISED PER ECO-12-021161 | 12.04.12 | G.WELLS  |
| K         | REVISED PER ECO-15-002200 | 11.02.15 | H.SMITH  |




## CODE 40 TINEL-LOCK ADAPTER

### NOTES:

1. THIS PRODUCT IS DESIGNED TO TERMINATE A BRAIDED CABLE SHIELD AND A HEAT SHRINKABLE LIPPED BOOT TO A CONNECTOR.
2. SEE CH00-0250-008 FOR ORDERING INFORMATION, MODIFICATIONS AND ADDITIONAL DIMENSIONS.
- ③ SEE DRAWING "TR" FOR DETAILS ON TINEL-LOCK RING. RINGS ARE DESIGNED TO BE HEATED ELECTRICALLY. ALL RINGS ARE MARKED WITH THERMOCHROMIC PAINT WHICH CHANGES COLOR WHEN INSTALLATION TEMPERATURE IS REACHED.
4. ADAPTER TO BE PERMANENTLY MARKED WITH CODE IDENT. NO. AND PART NO. LESS RING DESIGNATOR (E.G.: 06090-TXR40AB00-1206). RINGS SHALL BEAR NO MARKING.
- ⑤ FOR LARGER ENTRY SIZES, A 2 PIECE ADAPTER (TYPE II) IS SUPPLIED.
- ⑥ ADAPTER MATES TO MIL-C-38999, SERIES III AND IV, CLASS C, F, K, AND W, D38999/20, /24, /26, /40, /46, /47 CONNECTORS, AND WHEN SO MATED SHALL PROVIDE A WATER-TIGHT SEAL MEETING THE REQUIREMENTS OF MIL-C-85049, PAR. 3.5.7.
- ⑦ THESE DIMENSIONS APPLY IF A SELF-LOCKING COUPLING NUT IS USED. (MOD. CODE "S").
- ⑧ THESE DIMENSIONS APPLY IF AN ADAPTER MATERIAL IS STAINLESS STEEL.


©2015 Tyco Electronics Corporation. All rights reserved.

Raychem Adapters  
CUSTOMER DRAWING


|                                                                                                                                                           |                       |                          |                                                                                                                |              |  |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|--------------------------|----------------------------------------------------------------------------------------------------------------|--------------|--|
| UNLESS OTHERWISE SPECIFIED DIMENSIONS<br>ARE IN INCHES. METRIC DIMENSIONS ARE<br>IN BRACKETS.                                                             | DRAWN<br>R. RAMIREZ   | DATE<br>03-18-93         | <div>TE Connectivity</div> |              |  |
|                                                                                                                                                           | CHECKED               | DATE                     |                                                                                                                |              |  |
| TE CONNECTIVITY RESERVES THE RIGHT<br>TO AMEND THIS DRAWING AT ANY TIME.<br>USERS SHOULD EVALUATE THE SUITABILITY<br>OF THE PRODUCT FOR THEIR APPLICATION | APPROVED<br>W. C. GAY | DATE<br>05-19-93         | TITLE<br><br>TINEL-LOCK™ ADAPTER                                                                               |              |  |
|                                                                                                                                                           | APPROVED<br>G. WELLS  | DATE<br>11-15-12         |                                                                                                                |              |  |
| DECIMAL TOLERANCES                                                                                                                                        |                       |                          |                                                                                                                |              |  |
| .XXX ± 0.005 [0.13 mm]                                                                                                                                    |                       |                          |                                                                                                                |              |  |
| .XX ± 0.01 [0.25 mm]                                                                                                                                      |                       |                          |                                                                                                                |              |  |
| .X ± 0.1 [0.50 mm]                                                                                                                                        |                       |                          |                                                                                                                |              |  |
| ANGLE TOLERANCE                                                                                                                                           |                       |                          |                                                                                                                |              |  |
| .X ± 1 DEG.                                                                                                                                               |                       |                          |                                                                                                                |              |  |
| THIRD ANGLE<br>PROJECTION <div></div>                                  | SIZE<br>A             | CODE IDENT. NO.<br>06090 | DWG. NO.<br>TXR40                                                                                              | REV<br>K     |  |
|                                                                                                                                                           | DO NOT SCALE THIS DWG |                          |                                                                                                                | SHEET 1 OF 3 |  |
|                                                                                                                                                           |                       |                          |                                                                                                                |              |  |

If this document is printed it becomes uncontrolled. Check for the latest revision


SEE SHEET 1 FOR REVISION




STRAIGHT ADAPTER-TYPE I




STRAIGHT ADAPTER-TYPE II




45° ADAPTER-TYPE I



45° ADAPTER-TYPE II



90° ADAPTER  
TYPE I



90° ADAPTER  
TYPE II

Raychem Adapters  
CUSTOMER DRAWING

| SIZE                  | CODE IDENT. NO. | DWG. NO.           | REV          |
|-----------------------|-----------------|--------------------|--------------|
| A                     | 06090           | TXR40              | K            |
| DO NOT SCALE THIS DWG |                 | CAD NAME TXR40_2_K | SHEET 2 OF 3 |

| TABLE I   |                                                                                              |     |                                                                                                         |                       |                 |                                                                                             |                |                 |                |                |                                                                                           |
|-----------|----------------------------------------------------------------------------------------------|-----|---------------------------------------------------------------------------------------------------------|-----------------------|-----------------|---------------------------------------------------------------------------------------------|----------------|-----------------|----------------|----------------|-------------------------------------------------------------------------------------------|
| ORDER NO. | SHELL SIZE  |     | MAX ENTRY SIZE  TYPE I | A METRIC THD CLASS 6H | B DIA MAX       | B DIA MAX  | C MAX          | D MAX           | E MAX          | W MAX          | W MAX  |
|           | COM'L                                                                                        | MIL |                                                                                                         |                       |                 |                                                                                             |                |                 |                |                |                                                                                           |
| 08        | 9                                                                                            | A   | 04                                                                                                      | M12 X 1.0             | .750<br>[19.1]  | .969<br>[24.6]                                                                              | .82<br>[20.8]  | 1.075<br>[27.3] | 1.10<br>[27.9] | .85<br>[21.6]  | .85<br>[21.7]                                                                             |
| 10        | 11                                                                                           | B   | 07                                                                                                      | M15 X 1.0             | .850<br>[21.6]  | 1.063<br>[27.0]                                                                             | .84<br>[21.3]  | 1.102<br>[28.0] | 1.20<br>[30.5] | .97<br>[24.6]  | .97<br>[24.8]                                                                             |
| 12        | 13                                                                                           | C   | 08                                                                                                      | M18 X 1.0             | 1.000<br>[25.4] | 1.219<br>[31.0]                                                                             | .87<br>[22.1]  | 1.122<br>[28.5] | 1.26<br>[32.0] | 1.10<br>[27.9] | 1.13<br>[28.8]                                                                            |
| 14        | 15                                                                                           | D   | 10                                                                                                      | M22 X 1.0             | 1.150<br>[29.2] | 1.406<br>[35.7]                                                                             | .89<br>[22.6]  | 1.161<br>[29.5] | 1.34<br>[34.0] | 1.24<br>[31.5] | 1.24<br>[31.6]                                                                            |
| 16        | 17                                                                                           | E   | 12                                                                                                      | M25 X 1.0             | 1.280<br>[32.5] | 1.469<br>[37.3]                                                                             | .92<br>[23.4]  | 1.189<br>[30.2] | 1.40<br>[35.6] | 1.36<br>[34.5] | 1.36<br>[34.7]                                                                            |
| 18        | 19                                                                                           | F   | 14                                                                                                      | M28 X 1.0             | 1.400<br>[35.6] | 1.594<br>[40.5]                                                                             | .95<br>[24.1]  | 1.220<br>[31.0] | 1.45<br>[36.8] | 1.41<br>[35.8] | 1.53<br>[39.0]                                                                            |
| 20        | 21                                                                                           | G   | 16                                                                                                      | M31 X 1.0             | 1.500<br>[38.1] | 1.750<br>[44.5]                                                                             | .97<br>[24.6]  | 1.236<br>[31.4] | 1.51<br>[38.4] | 1.53<br>[38.9] | 1.62<br>[41.2]                                                                            |
| 22        | 23                                                                                           | H   | 18                                                                                                      | M34 X 1.0             | 1.650<br>[41.9] | 1.844<br>[46.8]                                                                             | 1.00<br>[25.4] | 1.244<br>[31.6] | 1.57<br>[39.9] | 1.67<br>[42.5] | 1.74<br>[44.2]                                                                            |
| 24        | 25                                                                                           | J   | 20                                                                                                      | M37 X 1.0             | 1.750<br>[44.5] | 2.031<br>[51.6]                                                                             | 1.02<br>[25.9] | 1.283<br>[32.6] | 1.67<br>[42.4] | 1.79<br>[45.5] | 1.84<br>[46.9]                                                                            |

| TABLE II   |                     |                                |                       |                |                |                |                |                |                                                                                                |
|------------|---------------------|--------------------------------|-----------------------|----------------|----------------|----------------|----------------|----------------|------------------------------------------------------------------------------------------------|
| ENTRY SIZE | Z<br>+.010<br>-.020 | S<br>DIA                       | Y<br>±.015<br>[±0.38] | F<br>MAX       | G<br>MAX       | H<br>MAX       | J<br>MAX       | K<br>MAX       | K<br>MAX  |
| 04         | .250<br>[6.35]      | .376 [9.56]<br>.370 [9.39]     | .550<br>[13.97]       | N/A            | N/A            | N/A            | N/A            | N/A            | N/A                                                                                            |
| 05         | .312<br>[7.92]      | .438 [11.13]<br>.432 [10.97]   | .612<br>[15.54]       | .77<br>[19.6]  | 1.10<br>[28.0] | 1.19<br>[30.2] | 1.16<br>[29.5] | .83<br>[21.0]  | .97<br>[24.6]                                                                                  |
| 06         | .375<br>[9.52]      | .501 [12.73]<br>.495 [12.57]   | .675<br>[17.14]       | .77<br>[19.6]  | 1.10<br>[28.0] | 1.19<br>[30.2] | 1.16<br>[29.5] | .83<br>[21.0]  | .97<br>[24.6]                                                                                  |
| 07         | .437<br>[11.09]     | .563 [14.31]<br>.556 [14.12]   | .737<br>[18.71]       | .80<br>[20.3]  | 1.10<br>[28.0] | 1.38<br>[35.1] | 1.22<br>[31.0] | .92<br>[23.4]  | .97<br>[24.6]                                                                                  |
| 08         | .500<br>[12.70]     | .626 [15.91]<br>.619 [15.72]   | .800<br>[20.32]       | .80<br>[20.3]  | 1.12<br>[28.5] | 1.38<br>[35.1] | 1.22<br>[31.0] | .96<br>[24.5]  | 1.11<br>[28.3]                                                                                 |
| 10         | .625<br>[15.87]     | .752 [19.11]<br>.742 [18.84]   | .925<br>[23.49]       | .84<br>[21.3]  | 1.16<br>[29.5] | 1.51<br>[38.4] | 1.35<br>[34.3] | 1.18<br>[30.0] | 1.28<br>[32.4]                                                                                 |
| 12         | .750<br>[19.05]     | .877 [22.28]<br>.867 [22.02]   | 1.050<br>[26.67]      | .88<br>[22.4]  | 1.19<br>[30.2] | 1.63<br>[41.4] | 1.40<br>[35.6] | 1.35<br>[34.3] | 1.40<br>[35.6]                                                                                 |
| 14         | .875<br>[22.23]     | 1.002 [25.46]<br>.991 [25.17]  | 1.175<br>[29.84]      | .88<br>[22.4]  | 1.22<br>[31.0] | 1.78<br>[45.2] | 1.46<br>[37.1] | 1.41<br>[35.8] | 1.51<br>[38.5]                                                                                 |
| 16         | 1.000<br>[25.40]    | 1.127 [28.63]<br>1.116 [28.34] | 1.300<br>[33.02]      | .93<br>[23.6]  | 1.24<br>[31.4] | 1.88<br>[47.8] | 1.53<br>[38.9] | 1.60<br>[40.6] | 1.64<br>[41.7]                                                                                 |
| 18         | 1.125<br>[28.57]    | 1.252 [31.81]<br>1.241 [31.52] | 1.425<br>[36.19]      | .93<br>[23.6]  | 1.25<br>[31.6] | 2.01<br>[51.1] | 1.59<br>[40.4] | 1.66<br>[42.2] | 1.73<br>[43.9]                                                                                 |
| 20         | 1.250<br>[31.75]    | 1.377 [34.98]<br>1.366 [34.69] | 1.550<br>[39.37]      | .98<br>[24.9]  | 1.28<br>[32.6] | 2.13<br>[54.1] | 1.78<br>[45.2] | 2.04<br>[51.8] | 2.04<br>[51.8]                                                                                 |
| 22         | 1.375<br>[34.93]    | 1.502 [38.15]<br>1.488 [37.79] | 1.675<br>[42.55]      | 1.03<br>[26.2] | 1.41<br>[35.8] | 2.29<br>[58.2] | 1.85<br>[47.0] | 2.23<br>[56.6] | 2.23<br>[56.6]                                                                                 |
| 24         | 1.500<br>[38.10]    | 1.627 [41.33]<br>1.613 [40.97] | 1.800<br>[45.72]      | 1.08<br>[27.2] | 1.52<br>[38.6] | 2.42<br>[61.5] | 1.92<br>[48.8] | 2.23<br>[56.6] | 2.23<br>[56.6]                                                                                 |

Raychem Adapters  
CUSTOMER DRAWING

| SIZE                  | CODE IDENT. NO. | DWG. NO.           | REV          |
|-----------------------|-----------------|--------------------|--------------|
| A                     | 06090           | TXR40              | K            |
| DO NOT SCALE THIS DWG |                 | CAD NAME TXR40_3_K | SHEET 3 OF 3 |