

SL... Stack Lights Modules

		Rated operational voltage U_e	Color	Type Article no.	Price See Price List
Basic module					
Black, with top cover					
 	With screw terminals			SL-B 205311	
	With Cage Clamp ¹⁾			SL-CB 218483	
	With connection capability to an AS-interface Base module (printed circuit board in housing has 3 outputs): • energy supply complete from AS-interface (max. 250 mA) with 2 screw terminals • combination of 3 function modules of differing functionality (continuous, blinking, strobe light, and acoustic module) • status display via LEDs • function modules ordered separately			SL-B-ASI ²⁾ 222174	
Continuous light module					
Without filament bulbs			 white	SL-L-W 205312	
			 red	SL-L-R 205313	
			 green	SL-L-G 205314	
			 yellow	SL-L-Y 205315	
			 blue	SL-L-B 205316	
Flashing light module					
Without filament bulb, also suitable for LED, $f \approx 1$ Hz		24 V AC/DC	 white	SL-BL24-W 205317	
			 red	SL-BL24-R 205318	
			 green	SL-BL24-G 205319	
			 yellow	SL-BL24-Y 205320	
			 blue	SL-BL24-B 205321	
		110 – 130 V AC	 white	SL-BL130-W 205322	
			 red	SL-BL130-R 205323	
			 green	SL-BL130-G 205324	
			 yellow	SL-BL130-Y 205325	
			 blue	SL-BL130-B 205326	
		230 V AC	 white	SL-BL230-W 205327	
			 red	SL-BL230-R 205328	
			 green	SL-BL230-G 205329	
			 yellow	SL-BL230-Y 205330	
			 blue	SL-BL230-B 205331	
	Acoustic indicator module				
84 – 92 dB in 60 cm					
	Continuous tone $f = 2750$ Hz	12 – 36 V AC/DC 8 – 12 mA		SL-A24 205341	
		110 – 230 V AC/DC 4 – 8 mA		SL-A110-230 205342	
	Pulsed tone 5 Hz at $f = 2750$ Hz	12 – 36 V AC/DC 8 – 12 mA		SL-AP24 205343	
		110 – 230 V AC/DC 4 – 8 mA		SL-AP110-230 205344	

Notes

- ¹⁾ Cage Clamp is a registered trademark of Wago Contact Technik GmbH, Minden, Germany
²⁾ To be used with LEDs only. UL/CSA pending