





# MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING  
DIMENSIONS IN METRIC - [ ]


This drawing is the property of  
Tusonix, Inc., and may not be  
used, reproduced, published or  
disclosed to others without ex-  
pressed authorization by Tusonix Inc.



Electrical Testing  
per Tusonix standard  
test plans and Mil-Std-202  
Test Methods.



## MOUNTING HARDWARE



## NOTES:

1. OPERATING TEMPERATURE RANGE: -55°C TO +125°C.
2. SILVER PLATED CASE, LEAD AND MOUNTING HARDWARE.
3. MAX. RECOMMENDED MOUNTING TORQUE : 2.0 lb. - in.
4. MAX. RECOMMENDED SOLDERING TEMPERATURE : 260°C. SEE INSTALLATION RECOMMENDATIONS.
5. NUT AND LOCK WASHER INCLUDED.
6. TUSONIX STANDARD PART NUMBER: 4403-040. TUSONIX RoHS COMPLIANT PART NUMBER: 4403-040 LF. CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
7. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.

STANDARD PART: BLACK INK. RoHS PART: GREEN INK.

27,000	GMV	70	50	10	10	28	42	65	65
CAP.(pf)	TOLERANCE	+85 °C	+125 °C	DC CURRENT	1 MHz	10 MHz	100 MHz	1 GHz	10 GHz
DC WORKING VOLTAGE									

--TOLERANCES--  
Unless Otherwise  
Specified

DECIMAL ± NOTED

ANGLES ± NOTED

Title

## MINI BUSHING STYLE EMI FILTER

Drawn S.M. 06-10-02 Scale 8 X

Approved J.Mc. 06-10-02

A

4403-040

**TUSONIX**  
TUCSON, ARIZONA

## REVISION RECORD

Original Release C.O. <b>6965</b>	<b>0</b>
-040 & -680 ADDED, DC WAS5. E.C. 11-20-92	
<b>7052</b>	<b>1</b>
RDN TO COMP FMT. S.M. 07-16-02	
<b>20020715-1-28</b>	<b>2</b>
ADDED AND REVISED NOTES. S.M. 06-07-06	
<b>20060605-7-02</b>	<b>3</b>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tusonix:

[4403-040LF](#)